

Double actuator pushbutton



**Part no.** M22-T-DD  
**216396**  
**EL Number** 4355415  
**(Norway)**

General specifications		
Product name		Eaton Moeller® series M22 Accessory Double actuator pushbutton
Part no.		M22-T-DD
EAN		4015082163969
Product Length/Depth		33 millimetre
Product height		23 millimetre
Product width		58 millimetre
Product weight		0.008 kilogram
Compliances		Contact Manufacturer
Certifications		CE
Product Tradename		M22
Product Type		Accessory
Product Sub Type		Double actuator pushbutton
Catalog Notes		Do not use in conjunction with M22S-ST legend plate mount, since degree of protection cannot be guaranteed Silicone transparent version for harsh environmental conditions and application in the food industry
Features & Functions		
Color		Colorless
Features		Transparent
Material		Silicone
Shape		Round
General information		
Degree of protection		NEMA 13 NEMA 12 NEMA 3R NEMA 4X
Model		Other
Protection		Additional protection for double actuator pushbuttons
Used with		Double actuator pushbuttons
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		70 °C
Communication		
Connection to SmartWire-DT		No
Contacts		
Force for positive opening - min		0 N
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		0 W
Rated operational current for specified heat dissipation (In)		0 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Please enquire
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of assemblies			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			Not applicable.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Protective cap for command devices (EC002040)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Protective cover for command devices (ecl@ss10.0.1-27-37-12-07 [ACO047011])			
Colour			Colourless
Transparent			Yes
Shape			Round
Model			Other