

Insert label, 18x27, aluminum, blank



Part no. M22-XST
216480
EL Number 4355430
(Norway)

General specifications		
Product name		Eaton Moeller® series M22 Accessory Insert label
Part no.		M22-XST
EAN		4015082164805
Product Length/Depth		1 millimetre
Product height		18 millimetre
Product width		27 millimetre
Product weight		0.4 gram
Compliances		Contact Manufacturer
Certifications		UL/CSA certification not required
Product Tradename		M22
Product Type		Accessory
Product Sub Type		Insert label
Features & Functions		
Color		Silver
Inscription		None
Language		Other
Material		Aluminum Acrylnitril-Butadien-Styrol-Copolymer (ABS) with aluminium hot stamping foil
Shape		Rectangular
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		70 °C
Communication		
Connection to SmartWire-DT		No
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		0 W
Rated operational current for specified heat dissipation (In)		0 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Please enquire
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.

10.10 Temperature rise			Not applicable.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Text plate for command devices (EC000624)

Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Identification plate for command devices (ecI@ss10.0.1-27-37-12-25 [AKF043014])

Meaning of the imprint			None
Language of the imprint			Other
Imprint ISO symbols			None
Colour			Silver
Shape			Rectangular
Width		mm	27
Height		mm	18
Outer diameter		mm	0