

**Motor-protective circuit-breaker, Ir= 50 - 58 A, Screw terminals,
Terminations: IP00**

Part no. PKZM4-58
222394
EL Number 4355162
(Norway)

General specifications	
Product name	Eaton Moeller® series PKZM4 Motor-protective circuit-breaker
Part no.	PKZM4-58
EAN	4015082223946
Product Length/Depth	160 millimetre
Product height	140 millimetre
Product width	55 millimetre
Product weight	1.136 kilogram
Certifications	UL File No.: E36332 UL IEC/EN 60947-4-1 UL Category Control No.: NLRV VDE 0660 CE CSA CSA-C22.2 No. 60947-4-1-14 CSA Class No.: 3211-05 UL 60947-4-1 CSA File No.: 165628 IEC/EN 60947
Product Tradename	PKZM4
Product Type	Motor-protective circuit-breaker
Product Sub Type	None
Catalog Notes	IE3-ready devices are identified by the logo on their packaging.
Features & Functions	
Actuator type	Turn button
Features	Phase-failure sensitivity (according to IEC/EN 60947-4-1, VDE 0660 Part 102)
Functions	Motor protection Phase failure sensitive
Number of poles	Three-pole
General information	
Connection	Screw terminals
Degree of protection	IP20 Terminals: IP00
Explosion safety category for dust	ATEX dust-ex-protection, PTB 10, ATEX 3012, Ex II(2) G
Lifespan, electrical	30,000 operations (at 400V, AC-3)
Lifespan, mechanical	30,000 Operations (Main conducting paths)
Mounting position	Can be snapped on to IEC/EN 60715 top-hat rail with 7.5 or 15 mm height.
Operating frequency	40 Operations/h
Overvoltage category	III
Pollution degree	3
Product category	Motor protective circuit breaker
Protection	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
Rated impulse withstand voltage (Uimp)	6000 V AC
Shock resistance	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
Suitable for	Also motors with efficiency class IE3 Branch circuit: Manual type E if used with terminal, or suitable for group installations, (UL/CSA)
Temperature compensation	-25 - 55 °C, Operating range -5 - 40 °C to IEC/EN 60947, VDE 0660 ≤ 0.25 %/K, residual error for T > 40°
Climatic environmental conditions	
Altitude	Max. 2000 m

Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	55 °C
Ambient operating temperature (enclosed) - min	25 °C
Ambient operating temperature (enclosed) - max	40 °C
Ambient storage temperature - min	40 °C
Ambient storage temperature - max	80 °C
Climatic proofing	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
Terminal capacities	
Terminal capacity (flexible with ferrule)	1 x (0.75 - 35) mm ² , Main cables 2 x (0.75 - 25) mm ² , Main cables
Terminal capacity (solid)	1 x (0.75 - 16) mm ² , Main cables 2 x (0.75 - 16) mm ²
Terminal capacity (solid/stranded AWG)	14 - 2
Stripping length (main cable)	14 mm
Tightening torque	3.3 Nm, Screw terminals, Main cable
Electrical rating	
Rated frequency - min	50 Hz
Rated frequency - max	60 Hz
Rated operational current (Ie)	58 A
Rated operational power at AC-3, 220/230 V, 50 Hz	17 kW
Rated operational power at AC-3, 380/400 V, 50 Hz	30 kW
Rated operational power at AC-3, 440 V, 50 Hz	37 kW
Rated operational power at AC-3, 500 V, 50 Hz	37 kW
Rated operational power at AC-3, 690 V, 50 Hz	55 kW
Rated operational voltage (Ue) - min	690 V
Rated operational voltage (Ue) - max	690 V
Rated uninterrupted current (Iu)	58 A
Short-circuit rating	
Rated short-circuit breaking capacity Icu at 400 V AC	50 kA
Short-circuit current	60 kA DC, up to 250 V DC, Main conducting paths
Short-circuit current rating (group protection)	600 A, 600 V High Fault, max. Fuse, SCCR (UL/CSA) 42 kA, 600 V High Fault, Fuse, SCCR (UL/CSA) 42 kA, 600 V High Fault, CB, SCCR (UL/CSA) 600 A, 600 V High Fault, max. CB, SCCR (UL/CSA)
Short-circuit current rating (type E)	Accessories required BK50/3-PKZ4-E 50 kA, 480 Y/277 V, SCCR (UL/CSA) 50 kA, 240 V, SCCR (UL/CSA)
Short-circuit release	899 A, I _{rm} , Setting range max. ± 20% tolerance, Trip blocks Basic device fixed 15.5 x I _u , Trip Blocks
Switching capacity	
Switching capacity	58 A (3 contacts in series), DC-5 up to 250V 58 A, AC-3 up to 690 V
Motor rating	
Assigned motor power at 230/240 V, 60 Hz, 1-phase	10 HP
Assigned motor power at 460/480 V, 60 Hz, 3-phase	40 HP
Assigned motor power at 575/600 V, 60 Hz, 3-phase	50 HP
Trip blocks	
Overload release current setting - min	50 A
Overload release current setting - max	58 A
Tripping characteristic	Overload trigger: tripping class 10 A
Design verification	
Equipment heat dissipation, current-dependent P _{vid}	28.2 W
Heat dissipation capacity P _{diss}	0 W
Heat dissipation per pole, current-dependent P _{vid}	9.4 W
Rated operational current for specified heat dissipation (I _n)	58 A
Static heat dissipation, non-current-dependent P _{vs}	0 W
10.2.2 Corrosion resistance	Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Motor protection circuit-breaker (EC000074)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Motor protection circuit-breaker (ecl@ss10.0.1-27-37-04-01 [AG2529016])		
Overload release current setting	A	50 - 58
Adjustment range undelayed short-circuit release	A	899 - 899
With thermal protection		No
Phase failure sensitive		Yes
Switch off technique		Thermomagnetic
Rated operating voltage	V	690 - 690
Rated permanent current I _u	A	58
Rated operation power at AC-3, 230 V	kW	17
Rated operation power at AC-3, 400 V	kW	30
Type of electrical connection of main circuit		Screw connection
Type of control element		Turn button
Device construction		Built-in device fixed built-in technique
With integrated auxiliary switch		No
With integrated under voltage release		No
Number of poles		3
Rated short-circuit breaking capacity I _{cu} at 400 V, AC	kA	50
Degree of protection (IP)		IP20
Height	mm	140
Width	mm	55
Depth	mm	160