

Contactors, 3 pole, 380 V 400 V 75 kW, RAC 240: 190 - 240 V 50/60 Hz, AC operation, Screw terminals



Part no. DILM150(RAC240)

239588

**EL Number
(Norway)**

4134058

| General specifications | | |
|--|--|---|
| Product name | | Eaton Moeller® series DILM contactor |
| Part no. | | DILM150(RAC240) |
| EAN | | 4015082395889 |
| Product Length/Depth | | 160 millimetre |
| Product height | | 170 millimetre |
| Product width | | 90 millimetre |
| Product weight | | 2.25 kilogram |
| Certifications | | CSA UL CSA-C22.2 No. 60947-4-1-14 VDE 0660 IEC/EN 60947 CE CSA File No.: 012528 UL File No.: E29096 IEC/EN 60947-4-1 UL 60947-4-1 CSA Class No.: 2411-03, 3211-04 UL Category Control No.: NLDX |
| Product Tradename | | DILM |
| Product Type | | Contactor |
| Product Sub Type | | None |
| Catalog Notes | | Contacts according to EN 50012 |
| Features & Functions | | |
| Fitted with: | | Suppressor circuit in actuating electronics |
| General information | | |
| Application | | Contactors for Motors |
| Degree of protection | | IP00 |
| Frame size | | FS4 |
| Lifespan, mechanical | | 10,000,000 Operations (AC operated) |
| Operating frequency | | 3600 mechanical Operations/h (AC operated) |
| Overvoltage category | | III |
| Pollution degree | | 3 |
| Product category | | Contactors |
| Protection | | Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274) |
| Rated impulse withstand voltage (Uimp) | | 8000 V AC |
| Residual current | | 1 mA (with actuation of A1 - A2 by the electronics with "0" signal) |
| Resistance per pole | | 0.6 mΩ |
| Suitable for | | Also motors with efficiency class IE3 |
| Utilization category | | AC-1: Non-inductive or slightly inductive loads, resistance furnaces AC-3: Normal AC induction motors: starting, switch off during running AC-4: Normal AC induction motors: starting, plugging, reversing, inching |
| Voltage type | | AC |
| Ambient conditions, mechanical | | |
| Shock resistance | | 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms |

| | | |
|---|--|--|
| | | 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms |
| Climatic environmental conditions | | |
| Altitude | | Max. 2000 m |
| Ambient operating temperature - min | | -25 °C |
| Ambient operating temperature - max | | 60 °C |
| Ambient operating temperature (enclosed) - min | | 25 °C |
| Ambient operating temperature (enclosed) - max | | 40 °C |
| Ambient storage temperature - min | | 40 °C |
| Ambient storage temperature - max | | 80 °C |
| Climatic proofing | | Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30 |
| Electro magnetic compatibility | | |
| Emitted interference | | According to EN 60947-1 |
| Interference immunity | | According to EN 60947-1 |
| Terminal capacities | | |
| Terminal capacity (copper band) | | 2 x (6 x 16 x 0.8) mm (Number of segments x width x thickness), Main cables |
| Terminal capacity (flexible with ferrule) | | 2 x (0.75 - 2.5) mm ² , Control circuit cables 1 x (10 - 95) mm ² , Main cables 2 x (10 - 70) mm ² , Main cables 1 x (0.75 - 2.5) mm ² , Control circuit cables |
| Terminal capacity (solid) | | 1 x (0.75 - 4) mm ² , Control circuit cables 2 x (0.75 - 2.5) mm ² , Control circuit cables |
| Terminal capacity (solid/stranded AWG) | | 18 - 14, Control circuit cables Single 8...3/0, double 8...2/0, Main cables |
| Terminal capacity (stranded) | | 1 x (16 - 95) mm ² , Main cables 2 x (16 - 70) mm ² , Main cables |
| Stripping length (main cable) | | 24 mm |
| Stripping length (control circuit cable) | | 10 mm |
| Screw size | | M10, Terminal screw, Main cables M3.5, Terminal screw, Control circuit cables 5 mm AF, Hexagon socket-head spanner, Terminal screw, Main cables |
| Screwdriver size | | 2, Terminal screw, Control circuit cables, Pozidriv screwdriver 0.8 x 5.5/1 x 6 mm, Terminal screw, Control circuit cables, Standard screwdriver |
| Tightening torque | | 14 Nm, Screw terminals, Main cables 1.2 Nm, Screw terminals, Control circuit cables |
| Electrical rating | | |
| Rated breaking capacity at 220/230 V | | 1500 A |
| Rated breaking capacity at 380/400 V | | 1500 A |
| Rated breaking capacity at 500 V | | 1500 A |
| Rated breaking capacity at 660/690 V | | 1200 A |
| Rated operational current (Ie) at AC-1, 380 V, 400 V, 415 V | | 190 A |
| Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V | | 150 A |
| Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V | | 150 A |
| Rated operational current (Ie) at AC-3, 440 V | | 150 A |
| Rated operational current (Ie) at AC-3, 500 V | | 150 A |
| Rated operational current (Ie) at AC-3, 660 V, 690 V | | 100 A |
| Rated operational current (Ie) at AC-4, 220 V, 230 V, 240 V | | 65 A |
| Rated operational current (Ie) at AC-4, 440 V | | 65 A |
| Rated operational current (Ie) at AC-4, 500 V | | 65 A |
| Rated operational current (Ie) at AC-4, 660 V, 690 V | | 50 A |
| Rated operational current (Ie) at DC-1, 60 V | | 160 A |
| Rated operational current (Ie) at DC-1, 110 V | | 160 A |
| Rated operational current (Ie) at DC-1, 220 V | | 90 A |
| Rated insulation voltage (Ui) | | 690 V |
| Rated making capacity up to 690 V (cos phi to IEC/EN 60947) | | 2100 A |
| Rated operational power at AC-3, 240 V, 50 Hz | | 52 kW |
| Rated operational power at AC-3, 380/400 V, 50 Hz | | 75 kW |
| Rated operational power at AC-3, 415 V, 50 Hz | | 91 kW |
| Rated operational power at AC-3, 440 V, 50 Hz | | 95 kW |

| | | |
|--|--|---|
| Rated operational power at AC-3, 500 V, 50 Hz | | 110 kW |
| Rated operational power at AC-3, 690 V, 50 Hz | | 96 kW |
| Rated operational power at AC-4, 220/230 V, 50 Hz | | 20 kW |
| Rated operational power at AC-4, 240 V, 50 Hz | | 22 kW |
| Rated operational power at AC-4, 415 V, 50 Hz | | 39 kW |
| Rated operational power at AC-4, 440 V, 50 Hz | | 41 kW |
| Rated operational power at AC-4, 500 V, 50 Hz | | 47 kW |
| Rated operational power at AC-4, 660/690 V, 50 Hz | | 48 kW |
| Rated operational voltage (Ue) at AC - max | | 690 V |
| Short-circuit rating | | |
| Short-circuit current rating (basic rating) | | 10 kA, SCCR (UL/CSA) 600 A, max. CB, SCCR (UL/CSA) 600 A, max. Fuse, SCCR (UL/CSA) |
| Short-circuit current rating (high fault at 480 V) | | 65 kA, CB, SCCR (UL/CSA) 250 A, max. CB, SCCR (UL/CSA) 300/300 A, Class J, max. Fuse, SCCR (UL/CSA) 30/100 kA, Fuse, SCCR (UL/CSA) |
| Short-circuit current rating (high fault at 600 V) | | 30/100 kA, Fuse, SCCR (UL/CSA) 300/600 A, Class J, max. Fuse, SCCR (UL/CSA) 30 kA, CB, SCCR (UL/CSA) 350 A, max. CB, SCCR (UL/CSA) |
| Short-circuit protection rating (type 1 coordination) at 400 V | | 250 A gG/gL |
| Short-circuit protection rating (type 1 coordination) at 690 V | | 250 A gG/gL |
| Short-circuit protection rating (type 2 coordination) at 400 V | | 250 A gG/gL |
| Short-circuit protection rating (type 2 coordination) at 690 V | | 250 A gG/gL |
| Conventional thermal current I_{th} | | |
| Conventional thermal current I _{th} (1-pole, enclosed) | | 360 A |
| Conventional thermal current I _{th} (3-pole, enclosed) | | 144 A |
| Conventional thermal current I _{th} at 55°C (3-pole, open) | | 170 A |
| Conventional thermal current I _{th} at 60°C (3-pole, open) | | 160 A |
| Conventional thermal current I _{th} of main contacts (1-pole, open) | | 400 A |
| Switching capacity | | |
| Switching capacity (main contacts, general use) | | 225 A, Maximum motor rating (UL/CSA) |
| Magnet system | | |
| Arcing time | | 15 ms |
| Drop-out voltage | | AC operated: 0.6 - 0.25 x UC, AC operated |
| Duty factor | | 100 % |
| Pick-up voltage | | 0.8 - 1.15 V AC x U _c |
| Power consumption, pick-up, 50 Hz | | 180 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz |
| Power consumption, pick-up, 60 Hz | | 170 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz |
| Power consumption, sealing, 50 Hz | | 2.3 W, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz 3.1 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz |
| Power consumption, sealing, 60 Hz | | 2.3 W, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz 3.1 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz |
| Rated control supply voltage (U _s) at AC, 50 Hz - min | | 190 V |
| Rated control supply voltage (U _s) at AC, 50 Hz - max | | 240 V |
| Rated control supply voltage (U _s) at AC, 60 Hz - min | | 190 V |
| Rated control supply voltage (U _s) at AC, 60 Hz - max | | 240 V |
| Rated control supply voltage (U _s) at DC - min | | 0 V |
| Rated control supply voltage (U _s) at DC - max | | 0 V |
| Switching time (AC operated, make contacts, closing delay) - min | | 28 ms |
| Switching time (AC operated, make contacts, closing delay) - max | | 33 ms |
| Switching time (AC operated, make contacts, opening delay) - min | | 35 ms |
| Switching time (AC operated, make contacts, opening delay) - max | | 41 ms |
| Motor rating | | |
| Assigned motor power at 115/120 V, 60 Hz, 1-phase | | 10 HP |
| Assigned motor power at 200/208 V, 60 Hz, 3-phase | | 50 HP |
| Assigned motor power at 230/240 V, 60 Hz, 1-phase | | 30 HP |
| Assigned motor power at 230/240 V, 60 Hz, 3-phase | | 60 HP |

| | | |
|--|--|--|
| Assigned motor power at 460/480 V, 60 Hz, 3-phase | | 125 HP |
| Assigned motor power at 575/600 V, 60 Hz, 3-phase | | 125 HP |
| Communication | | |
| Connection | | Screw terminals |
| Connection to SmartWire-DT | | No |
| Contacts | | |
| Number of auxiliary contacts (normally closed contacts) | | 0 |
| Number of auxiliary contacts (normally open contacts) | | 0 |
| Safety | | |
| Safe isolation | | 690 V AC, Between the contacts, According to EN 61140 690 V AC, Between coil and contacts, According to EN 61140 |
| Special purpose ratings | | |
| Special purpose rating of ballast electrical discharge lamps | | 160 A (600V 60Hz 3phase, 347V 60Hz 1phase) 160 A (480V 60Hz 3phase, 277V 60Hz 1phase) |
| Special purpose rating of definite purpose rating | | 150 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 900 A, LRA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) |
| Special purpose rating of elevator control | | 75 HP, 480 V 60 Hz 3-ph, (UL/CSA) 99 A, 600 V 60 Hz 3-ph, (UL/CSA) 104 A, 240 V 60 Hz 3-ph, (UL/CSA) 40 HP, 240 V 60 Hz 3-ph, (UL/CSA) 30 HP, 200 V 60 Hz 3-ph, (UL/CSA) 96 A, 480 V 60 Hz 3-ph, (UL/CSA) 100 HP, 600 V 60 Hz 3-ph, (UL/CSA) 92 A, 200 V 60 Hz 3-ph, (UL/CSA) |
| Special purpose rating of refrigeration control (CSA only) | | 540 A, LRA 600 V 60 Hz 3phase; (CSA) 540 A, LRA 480 V 60 Hz 3phase; (CSA) 90 A, FLA 600 V 60 Hz 3phase; (CSA) 90 A, FLA 480 V 60 Hz 3phase; (CSA) |
| Special purpose rating of resistance air heating | | 160 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) 160 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) |
| Special purpose rating of tungsten incandescent lamps | | 160 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) 160 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) |
| Design verification | | |
| Equipment heat dissipation, current-dependent Pvid | | 32.1 W |
| Heat dissipation capacity P _{diss} | | 0 W |
| Heat dissipation per pole, current-dependent Pvid | | 10.7 W |
| Rated operational current for specified heat dissipation (I _n) | | 150 A |
| Static heat dissipation, non-current-dependent P _{vs} | | 2.3 W |
| 10.2.2 Corrosion resistance | | Meets the product standard's requirements. |
| 10.2.3.1 Verification of thermal stability of enclosures | | Meets the product standard's requirements. |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat | | Meets the product standard's requirements. |
| 10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects | | Meets the product standard's requirements. |
| 10.2.4 Resistance to ultra-violet (UV) radiation | | Meets the product standard's requirements. |
| 10.2.5 Lifting | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions | | Meets the product standard's requirements. |
| 10.3 Degree of protection of assemblies | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 Clearances and creepage distances | | Meets the product standard's requirements. |
| 10.5 Protection against electric shock | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 Internal electrical circuits and connections | | Is the panel builder's responsibility. |
| 10.8 Connections for external conductors | | Is the panel builder's responsibility. |
| 10.9.2 Power-frequency electric strength | | Is the panel builder's responsibility. |
| 10.9.3 Impulse withstand voltage | | Is the panel builder's responsibility. |
| 10.9.4 Testing of enclosures made of insulating material | | Is the panel builder's responsibility. |
| 10.10 Temperature rise | | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 Electromagnetic compatibility | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |

Technical data ETIM 8.0

| | | |
|---|----|------------------|
| Low-voltage industrial components (EG000017) / Power contactor, AC switching (EC000066) | | |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Contactor (LV) / Power contactor, AC switching (ecl@ss10.0.1-27-37-10-03 [AAB718015]) | | |
| Rated control supply voltage Us at AC 50HZ | V | 190 - 240 |
| Rated control supply voltage Us at AC 60HZ | V | 190 - 240 |
| Rated control supply voltage Us at DC | V | 0 - 0 |
| Voltage type for actuating | | AC |
| Rated operation current Ie at AC-1, 400 V | A | 190 |
| Rated operation current Ie at AC-3, 400 V | A | 150 |
| Rated operation power at AC-3, 400 V | kW | 75 |
| Rated operation current Ie at AC-4, 400 V | A | 65 |
| Rated operation power at AC-4, 400 V | kW | 33 |
| Rated operation power NEMA | kW | 93 |
| Modular version | | No |
| Number of auxiliary contacts as normally open contact | | 0 |
| Number of auxiliary contacts as normally closed contact | | 0 |
| Type of electrical connection of main circuit | | Screw connection |
| Number of normally closed contacts as main contact | | 0 |
| Number of normally open contacts as main contact | | 3 |