



Miniature circuit breaker (MCB), 100A, 1p, B-Char, AC



Part no. PLHT-B100
Catalog No. 247979

Delivery program

| | | | |
|---|----------|----|--|
| Basic function | | | Miniature circuit-breakers |
| Number of poles | | | 1 pole |
| Tripping characteristic | | | B |
| Application | | | Switchgear for industrial and advanced commercial applications |
| Rated current | I_n | A | 100 |
| Rated switching capacity acc. to IEC/EN 60947-2 | I_{cu} | kA | 20 |
| Product range | | | PLHT |

Technical data

Electrical

| | | | |
|---|----------|----|----|
| Rated switching capacity acc. to IEC/EN 60947-2 | I_{cu} | kA | 20 |
|---|----------|----|----|

Design verification as per IEC/EN 61439

| | | | |
|--|------------|----|--|
| Technical data for design verification | | | |
| Rated operational current for specified heat dissipation | I_n | A | 100 |
| Heat dissipation per pole, current-dependent | P_{vid} | W | 0 |
| Equipment heat dissipation, current-dependent | P_{vid} | W | 9.1 |
| Static heat dissipation, non-current-dependent | P_{vs} | W | 0 |
| Heat dissipation capacity | P_{diss} | W | 0 |
| Operating ambient temperature min. | | °C | -25 |
| Operating ambient temperature max. | | °C | 55 |
| | | | linear, per +1 °C, results in a 0.35% reduction of current carrying capacity |
| IEC/EN 61439 design verification | | | |
| 10.2 Strength of materials and parts | | | |
| 10.2.2 Corrosion resistance | | | Meets the product standard's requirements. |
| 10.2.3.1 Verification of thermal stability of enclosures | | | Meets the product standard's requirements. |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat | | | Meets the product standard's requirements. |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects | | | Meets the product standard's requirements. |
| 10.2.4 Resistance to ultra-violet (UV) radiation | | | Meets the product standard's requirements. |
| 10.2.5 Lifting | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 Mechanical impact | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 Inscriptions | | | Meets the product standard's requirements. |
| 10.3 Degree of protection of ASSEMBLIES | | | |
| 10.4 Clearances and creepage distances | | | Meets the product standard's requirements. |
| 10.5 Protection against electric shock | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 Incorporation of switching devices and components | | | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 Internal electrical circuits and connections | | | Is the panel builder's responsibility. |
| 10.8 Connections for external conductors | | | Is the panel builder's responsibility. |
| 10.9 Insulation properties | | | |
| 10.9.2 Power-frequency electric strength | | | Is the panel builder's responsibility. |
| 10.9.3 Impulse withstand voltage | | | Is the panel builder's responsibility. |
| 10.9.4 Testing of enclosures made of insulating material | | | Is the panel builder's responsibility. |
| 10.10 Temperature rise | | | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |

| | | |
|-------------------------------------|--|--|
| 10.11 Short-circuit rating | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 Electromagnetic compatibility | | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.13 Mechanical function | | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Miniature circuit breaker (MCB) (EC000042)

Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Miniature circuit breaker (MCB)
(ecl@ss10.0.1-27-14-19-01 [AAB905014])

| | | |
|---|-----------------|----------|
| Release characteristic | | B |
| Number of poles (total) | | 1 |
| Number of protected poles | | 1 |
| Rated current | A | 100 |
| Rated voltage | V | 400 |
| Rated insulation voltage U_i | V | 440 |
| Rated impulse withstand voltage U_{imp} | kV | 4 |
| Rated short-circuit breaking capacity I_{cn} EN 60898 at 230 V | kA | 0 |
| Rated short-circuit breaking capacity I_{cn} EN 60898 at 400 V | kA | 0 |
| Rated short-circuit breaking capacity I_{cu} IEC 60947-2 at 230 V | kA | 20 |
| Rated short-circuit breaking capacity I_{cu} IEC 60947-2 at 400 V | kA | 20 |
| Voltage type | | AC |
| Frequency | Hz | 50 - 60 |
| Current limiting class | | 3 |
| Suitable for flush-mounted installation | | No |
| Concurrently switching N-neutral | | No |
| Over voltage category | | 3 |
| Pollution degree | | 2 |
| Additional equipment possible | | Yes |
| Width in number of modular spacings | | 1.5 |
| Built-in depth | mm | 69.5 |
| Degree of protection (IP) | | IP20 |
| Ambient temperature during operating | °C | -25 - 55 |
| Connectable conductor cross section multi-wired | mm ² | 2.5 - 50 |
| Connectable conductor cross section solid-core | mm ² | 2.5 - 50 |