



**Auxiliary contact, 1N/O+1N/C, 4A, 250V AC**

**Part no. Z-AHK**  
**Catalog No. 248433**

**EL-Nummer (Norway) 0001609492**

### Delivery program

Basic function		Accessories for combined residual-current/power circuit-breakers Accessories for residual current circuit-breakers Accessories for miniature circuit-breaker
Basic function accessories		Auxiliary contacts
Application		Switchgear for industrial and advanced commercial applications
Product range		Accessory
Side mounting		for fitting on left to: LS, FI/LS
Contact sequence		

### Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.	°C		-5
Operating ambient temperature max.	°C		40

### Technical data ETIM 7.0

Devices for distribution board-/surface mounting (EG000062) / Auxiliary device for distribution board devices (EC001286)			
Electric engineering, automation, process control engineering / Electrical installation, device / Breaker switch component / Auxiliary contact unit for distribution board (ecl@ss10.0.1-27-14-35-02 [AKE327013])			
Device fitting			Universal
Additional equipment			Auxiliary switch
Attached at delivery			No
Assembly width (TE)			0.5
Number of contacts as normally open contact			1
Number of contacts as normally closed contact			1
Number of contacts as change-over contact			0
Number of fault-signal switches			0
Rated switch current	A		3
Rated voltage	V		230
Voltage type for actuating			AC
With auto test for earth leakage function			No
Suitable for max. number of poles main contact unit (total)			2
Suitable for max. current main contact unit	A		4

## Dimensions

