

Auxiliary contact, 1N/O+1N/C, 4A, 250V AC



Part no. Z-AHK
248433
EL Number 1609492
(Norway)

General specifications		
Product name		Eaton Distribution parts
Part no.		Z-AHK
EAN		4015082484330
Product Length/Depth		80 millimetre
Product height		75 millimetre
Product width		8.8 millimetre
Product weight		0.038 kilogram
Compliances		RoHS conform
Certifications		EN45545-2 IEC 61373
Product Tradename		None
Product Type		Distribution parts
Product Sub Type		None
Public Consumption		Yes
Product Family Description		ES-PMCC-PDC-Eaton Distribution parts
Globally Marketable		Yes
Product Specification Details		
Accessory/spare part type		Auxiliary contacts
Additional equipment required		Auxiliary switch
Ambient operating temperature - max		40 °C
Ambient operating temperature - min		-5 °C
Application		Switchgear for industrial and advanced commercial applications
Assembly width		0.5
Device fitting		Universal
EL number		1609492
Functions		Auxiliary switch
Number of contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		1
Number of contacts (normally open contacts)		1
Number of poles at main contact unit - max		2
Number of switches (fault signal)		0
Rated operational voltage (Ue) - max		230 V
Rated switch current		3 A
Suitable for current of main contact unit - max		4 A
Type		Accessory Accessory for combined residual current/power circuit breaker Accessory for miniature circuit breaker Accessory for residual current circuit breaker
Used with		Auxiliary contacts Accessory for combined residual current/power circuit breaker Accessory Accessory for miniature circuit breaker Accessory for residual current circuit breaker
Voltage type		AC

Technical data ETIM 8.0

Devices for distribution board-/surface mounting (EG000062) / Auxiliary device for distribution board devices (EC001286)		
Electric engineering, automation, process control engineering / Electrical installation, device / Breaker switch component / Auxiliary contact unit for distribution board (ecI@ss10.0.1-27-14-35-02 [AKE327013])		
Device fitting		Universal

Additional equipment			Auxiliary switch
Installed at the factory			No
Width in number of modular spacings			0.5
Number of contacts as normally open contact			1
Number of contacts as normally closed contact			1
Number of contacts as change-over contact			0
Number of fault-signal switches			0
Rated switch current		A	3
Rated voltage		V	230
Voltage type for actuating			AC
With auto test for earth leakage function			No
Suitable for max. number of poles main contact unit (total)			2
Suitable for max. current main contact unit		A	4