



Modular PLC, 24 V DC, 8DI, 6DO, RS232, CAN, 64kB



Part no. **XC-CPU101-C64K-8DI-6DO**  
 Catalog No. **262152**  
 Alternate Catalog No. **XC-CPU101-C64K**  
 EL-Nummer (Norway) **4519630**

**Delivery program**

Digital input count			Digital: 8; of which usable as interrupt: 4
Quantity of outputs			Transistor: 6
Built-in interfaces			CANopen®/easyNet RS232
Instructions			expandable with → expansions XI/OC Only on connection with →XI/OC rack
User memory			64 Kbyte
Cycle time for 1 k of instructions (Bit, Byte)		ms	0.5
<b>Memory</b>			
Application/marker/retain data			64 KB/4 KB/4 KB
Integrated Web server			no
Information about equipment supplied			The following accessory equipment is required: terminal clamps, module rack, battery
Approvals			EAC

**Technical data**

**General**

Standards			IEC/EN 61131-2 EN 50178
Ambient temperature		°C	0 - +55
Storage	θ	°C	-25 - +70
Mounting position			Horizontal
Relative humidity, non-condensing (IEC/EN 60068-2-30)		%	10 - 95
Air pressure (operation)		hPa	795 - 1080
Vibration resistance			10 - 57 Hz ±0.075 mm 57 - 150 Hz ±1.0 g
Mechanical shock resistance		g	15 Shock duration 11 ms
Overvoltage category/pollution degree			II/2
Degree of Protection			IP20
Rated insulation voltage	U <sub>i</sub>	V	500
Emitted interference			EN 50081-2, Class A
Interference immunity			EN 50081-2
Battery (service life)			normally 5 years
Weight		kg	0.23
Terminations			Plug-in terminal block
Terminal capacities		mm <sup>2</sup>	
Screw terminals			
Flexible with ferrule		mm <sup>2</sup>	0.5 - 1.5
Solid		mm <sup>2</sup>	0.5 - 2.5
Spring-loaded terminals			
flexible		mm <sup>2</sup>	0.34 - 1.0
Solid		mm <sup>2</sup>	0.14 - 1.0

**Power supply**

Duration of mains dip		ms	10
Repetition rate		s	1
Input voltage		V DC	24

Admissible range		V DC	20.4 - 28.8
Input rating		W	max. 26
Residual ripple		%	≤ 5
Maximum power loss (without local I/O)	P <sub>v</sub>	W	6
Note on heat dissipation			Without local I/O
Overvoltage protection			Yes
Protection against polarity reversal			Yes
Mains filter (external)			Yes
Inrush current		x I <sub>n</sub>	No limitation (limited only by upstream 24 V DC power supply unit)
Signal module output voltage			
Rated value		V DC	5
Output current		A	3.2
Short-circuit rating			Yes
Electrically isolated from the supply voltage			No

## CPU

Processor			Infineon C164
-----------	--	--	---------------

## Memory

Program code and program data		kByte	64/64
Marker/retentive data		KByte	4/4
Cycle time for 1 k of instructions (Bit, Byte)		ms	< 0.5

## Interfaces

Serial interface (RS232) without handshake lines			
Data transfer rate		kbit/s	max. 57.6
Connection technique			RJ45
Potential isolation			No
CANopen®			
Maximum data transfer rate		Bits/s	500000
Potential isolation			Yes
Device profile			To DS 301 V4
PDO type			Asyn., cyc., acyc.
Connection			Plug-in terminal block
Bus terminating resistors			External
Stations		Number	max. 126
Watchdog			Yes
RTC (real-time clock)			Yes

## Power supply of local inputs/outputs (24 V<sub>0</sub>/0 V<sub>0</sub>)

Input voltage		V DC	24
Voltage range		V DC	19.2 - 30, note polarity
Potential isolation			
Power supply against CPU voltage			Yes
Overvoltage protection			Yes
Protection against polarity reversal			Yes

## Digital inputs

Input current per channel at nominal voltage		mA	Normally 3.5
Power loss per channel			Normally 85 mW
Voltage level to IEC/EN 61131-2			
Limit value type 1			Low < 5 V DC, high > 15 V DC
Input delay			
Off → On		ms	Normally 0.1
On → Off		ms	Normally 0.1
Inputs		Number	8 (4 of which are interrupt inputs)
Channels with the same reference potential		Qty.	8
Status indication			LED

## Digital outputs

Channels		Number	6
Power loss per channel		W	0.08

QX0.0 to QX0.3		A	0.5
Output delay			
Off → On			Normally 0.1 ms
On → Off			Normally 0.1 ms
Channels with the same reference potential		Qty.	6
Status indication			LED
Switching capacity			IEC/EN 60947-5-1, utilization category DC-13
duty factor		% DF	100
Utilization factor		g	1

## Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	$I_n$	A	0
Heat dissipation per pole, current-dependent	$P_{vid}$	W	0
Equipment heat dissipation, current-dependent	$P_{vid}$	W	0
Static heat dissipation, non-current-dependent	$P_{vs}$	W	6
Heat dissipation capacity	$P_{diss}$	W	0
Operating ambient temperature min.		°C	0
Operating ambient temperature max.		°C	55
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			
			Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures			
			Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat			
			Meets the product standard's requirements.
10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			
			Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation			
			Meets the product standard's requirements.
10.2.5 Lifting			
			Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact			
			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			
			Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES			
			Meets the product standard's requirements.
10.4 Clearances and creepage distances			
			Meets the product standard's requirements.
10.5 Protection against electric shock			
			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			
			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			
			Is the panel builder's responsibility.
10.8 Connections for external conductors			
			Is the panel builder's responsibility.
10.9 Insulation properties			
10.9.2 Power-frequency electric strength			
			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			
			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			
			Is the panel builder's responsibility.
10.10 Temperature rise			
			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			
			Is the panel builder's responsibility.
10.12 Electromagnetic compatibility			
			Is the panel builder's responsibility.
10.13 Mechanical function			
			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 7.0

PLC's (EG000024) / PLC CPU-module (EC000236)			
Electric engineering, automation, process control engineering / Control / Programmable logic control (SPS) / SPS - basic device (ecI@ss10.0.1-27-24-22-07 [AKE530014])			
Supply voltage AC 50 Hz		V	0 - 0
Supply voltage AC 60 Hz		V	0 - 0
Supply voltage DC		V	20.4 - 28.8
Voltage type of supply voltage			DC
Number of relay outputs			0
Max. number of time switches			1000

Model		Modular
Processing time (1K, binary operation)	ms	0.5
Number of HW-interfaces industrial Ethernet		0
Number of interfaces PROFINET		0
Number of HW-interfaces RS-232		1
Number of HW-interfaces RS-422		0
Number of HW-interfaces RS-485		0
Number of HW-interfaces USB		0
Number of HW-interfaces parallel		0
Number of HW-interfaces Wireless		0
Number of HW-interfaces other		1
Number of analogue outputs		0
Number of analogue inputs		0
Number of digital inputs		8
Number of digital outputs		6
With optical interface		No
Supporting protocol for TCP/IP		No
Supporting protocol for PROFIBUS		Yes
Supporting protocol for CAN		Yes
Supporting protocol for INTERBUS		No
Supporting protocol for ASI		No
Supporting protocol for KNX		No
Supporting protocol for MODBUS		Yes
Supporting protocol for Data-Highway		No
Supporting protocol for DeviceNet		No
Supporting protocol for SUCONET		Yes
Supporting protocol for LON		No
Supporting protocol for PROFINET IO		No
Supporting protocol for PROFINET CBA		No
Supporting protocol for SERCOS		No
Supporting protocol for Foundation Fieldbus		No
Supporting protocol for EtherNet/IP		No
Supporting protocol for AS-Interface Safety at Work		No
Supporting protocol for DeviceNet Safety		No
Supporting protocol for INTERBUS-Safety		No
Supporting protocol for PROFIsafe		No
Supporting protocol for SafetyBUS p		No
Supporting protocol for other bus systems		Yes
Radio standard Bluetooth		No
Radio standard WLAN 802.11		No
Radio standard GPRS		No
Radio standard GSM		No
Radio standard UMTS		No
IO link master		No
System accessory		Yes
Redundancy		No
With display		No
Type of memory		RAM
Memory size	kByte	64
Additional program memory possible		Yes
Rail mounting possible		Yes
Wall mounting/direct mounting		Yes
Front build in possible		No
Rack-assembly possible		No
Suitable for safety functions		No

Category according to EN 954-1			
SIL according to IEC 61508			None
Performance level acc. EN ISO 13849-1			None
Appendant operation agent (Ex ia)			No
Appendant operation agent (Ex ib)			No
Explosion safety category for gas			None
Explosion safety category for dust			None
Width		mm	60
Height		mm	100
Depth		mm	100

## Approvals

Product Standards			IEC: see Technical Data; UL508; CSA-C22.2 No. 0-M; CSA-C22.2 No. 142-M; CE marking
UL File No.			E135462
UL Category Control No.			NRAQ
CSA File No.			012528
CSA Class No.			2252-01
North America Certification			UL listed, CSA certified
Specially designed for North America			No
Current Limiting Circuit-Breaker			No
Degree of Protection			IEC: IP20, UL/CSA Type: -

## Dimensions

