

Installation contactor, 24VAC/50Hz, 4N/O, 25A, 2HP



Part no. **Z-SCH24/25-40**
248851

General specifications		
Product name		Eaton Distribution parts
Part no.		Z-SCH24/25-40
EAN		4015082488512
Product Length/Depth		85 millimetre
Product height		60 millimetre
Product width		35 millimetre
Product weight		0.22 kilogram
Compliances		RoHS conform
Product Tradename		None
Product Type		Distribution parts
Product Sub Type		None
Public Consumption		Yes
Product Family Description		ES-PMCC-PDC-Eaton Distribution parts
Globally Marketable		Yes
Product Specification Details		
Ambient operating temperature - max		60 °C
Ambient operating temperature - min		-40 °C
Amperage Rating		25 A
Built-in depth		60 mm
Degree of protection		IP40
Equipment heat dissipation, current-dependent		10 W
Features		Additional equipment possible
Heat dissipation capacity		0 W
Heat dissipation per pole, current-dependent		0 W
Incandescent lamp load - max		3000 W
Load fluorescent lamp (duo circuit) - max		2552 V-A
Load fluorescent lamp (parallel compensated) - max		1044 V-A
Load fluorescent lamp - max		1160 V-A
Number of contacts (normally closed contacts)		0
Number of contacts (normally open contacts)		4
Number of modular spacings		2
Rated operating voltage (Ue) - max		440 V
Rated operating voltage (Ue) - min		440 V
Rated operational current for specified heat dissipation (In)		25 A
Static heat dissipation, non-current-dependent		0 W
Utility category		1
Utilization category (according to EN IEC 60947-4-1)		AC-1
Voltage rating (excitation) - max		26.4 V
Voltage rating (excitation) - min		20.4 V
Voltage type		AC

Technical data ETIM 8.0

Devices for distribution board-/surface mounting (EG000062) / Installation contactor for distribution board (EC001653)		
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Installation contactor for distribution board (ecl@ss10.0.1-27-14-23-08 [AFZ820015])		
Rated operating voltage	V	440 - 440
Rated operation current	A	25
Utility category		1

Rated excitation voltage	V	20.4 - 26.4
Voltage type (operating voltage)		AC
Voltage type (excitation voltage)		AC
Number of contacts as normally open contact		4
Number of contacts as normally closed contact		0
Max. incandescent lamp load	W	3000
Max. load fluorescent lamp	VA	1160
Max. load fluorescent lamp (Duo circuit)	VA	2552
Max. load fluorescent lamp (parallel compensated)	VA	1044
Slider for hand switch		No
Width in number of modular spacings		2
Built-in depth	mm	60
Additional equipment possible		Yes
With day/night function		No
Hum-free		No
Degree of protection (IP)		IP40