

Contactor relay, 24 V DC, 4 N/O, Screw terminals, DC operation

Part no. **DILA-40(24VDC)**
276344
EL Number **4130203**
(Norway)

General specifications	
Product name	Eaton Moeller® series DILA Control Relay
Part no.	DILA-40(24VDC)
EAN	4015082763442
Product Length/Depth	75 millimetre
Product height	68 millimetre
Product width	45 millimetre
Product weight	0.296 kilogram
Certifications	CSA-C22.2 No. 14-05 UL File No.: E29184 IEC/EN 60947-4-1 CSA Class No.: 3211-03 IEC/EN 60947 VDE 0660 CSA EN 60947-5-1 UL Category Control No.: NKCR UL CE CSA File No.: 012528 UL 508
Product Tradename	DILA
Product Type	Control Relay
Product Sub Type	None
Catalog Notes	Coil terminal markings according to EN 50005 Contact numbers according to EN 50011 Rated operational current: Switch-on and switch-off conditions based on DC-13, time constant as specified.
Features & Functions	
Features	Positive operating contacts to EN 60947-5-1 appendix L, including auxiliary contact module
Fitted with:	Suppressor circuit Positive operation contacts Built-in suppressor circuit
General information	
Application	Contactor relays
Degree of protection	IP20
Shock resistance	5 g, N/C auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
Lifespan, mechanical	20,000,000 Operations (DC operated)
Mounting method	DIN-rail/screw
Operating frequency	9000 Operations/h
Overvoltage category	III
Pollution degree	3
Product category	DILA relays
Protection	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
Rated impulse withstand voltage (Uimp)	6000 V AC
Voltage type	DC
Climatic environmental conditions	
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	60 °C
Ambient operating temperature (enclosed) - min	25 °C
Ambient operating temperature (enclosed) - max	40 °C

Ambient storage temperature - min		40 °C
Ambient storage temperature - max		80 °C
Climatic proofing		Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
Terminal capacities		
Terminal capacity (flexible with ferrule)		2 x (0.75 - 2.5) mm ² , Screw terminals 1 x (0.75 - 2.5) mm ² , Screw terminals
Terminal capacity (solid)		2 x (0.75 - 2.5) mm ² , Screw terminals 1 x (0.75 - 4) mm ² , Screw terminals
Terminal capacity (solid/stranded AWG)		18 - 14, Screw terminals
Stripping length (main cable)		10 mm
Screw size		M3.5, Terminal screw
Screwdriver size		2, Terminal screw, Pozidriv screwdriver 0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver
Tightening torque		1.2 Nm, Screw terminals
Electrical rating		
Conventional thermal current I _{th} at 60°C (3-pole, open)		16 A
Rated operational current (I _e)		10 A at 24 V, DC L/R ≤ 15 ms (with 1 contact in series) 6 A at 110 V, DC L/R ≤ 15 ms (with 3 contacts in series) 4 A at 24 V, DC L/R ≤ 50 ms (with 3 contacts in series) 3 A at 110 V, DC L/R ≤ 15 ms (with 1 contact in series) 5 A at 220 V, DC L/R ≤ 15 ms (with 3 contacts in series) 4 A at 60 V, DC L/R ≤ 50 ms (with 3 contacts in series) 6 A at 60 V, DC L/R ≤ 15 ms (with 1 contact in series) 1 A at 220 V, DC L/R ≤ 50 ms (with 3 contacts in series) 10 A at 60 V, DC L/R ≤ 15 ms (with 2 contacts in series) 1 A at 220 V, DC L/R ≤ 15 ms (with 1 contact in series) 2 A at 110 V, DC L/R ≤ 50 ms (with 3 contacts in series) 16 A
Rated operational current (I _e) at AC-15, 220 V, 230 V, 240 V		4 A
Rated operational current (I _e) at AC-15, 380 V, 400 V, 415 V		4 A
Rated operational current (I _e) at AC-15, 500 V		1.5 A
Rated insulation voltage (U _i)		690 V
Rated operational voltage (U _e) at AC - max		690 V
Short-circuit protection rating without welding		10 A gG/gL, 500 V, Max. Fuse, Contacts
Safe isolation		400 V AC, Between coil and auxiliary contacts, According to EN 61140 400 V AC, Between auxiliary contacts, According to EN 61140
Switching capacity (auxiliary contacts, general use)		15 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA)
Switching capacity (auxiliary contacts, pilot duty)		A600, AC operated (UL/CSA) P300, DC operated (UL/CSA)
Magnet system		
Duty factor		100 %
Pick-up voltage		0.7 - 1.3 V DC x U _c (at 24 V: without auxiliary contact module and at ambient air temperature + 40 °C) 0.8 - 1.1 V DC x U _c
Power consumption (pick-up) at DC		2.6 W
Power consumption (sealing) at DC		2.6 W
Rated control supply voltage (U _s) at AC, 50 Hz - min		0 V
Rated control supply voltage (U _s) at AC, 50 Hz - max		0 V
Rated control supply voltage (U _s) at AC, 60 Hz - min		0 V
Rated control supply voltage (U _s) at AC, 60 Hz - max		0 V
Rated control supply voltage (U _s) at DC - min		24 V
Rated control supply voltage (U _s) at DC - max		24 V
Switching time (DC operated, make contacts, closing delay) - max		31 ms
Switching time (DC operated, make contacts, opening delay) - max		12 ms
Voltage tolerance		Smoothed DC, three-phase bridge rectifiers or smoothed double-wave rectification
Communication		
Connection to SmartWire-DT		In conjunction with DIL-SWD SmartWire DT contactor module Yes
Contacts		
Code number		40E

Control circuit reliability		< 2 λ, < 1 failure at 100,000,000 Operations (at U# = 24 V DC, Umin = 17 V, Imin = 5.4 mA)
Number of auxiliary contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		0
Number of contacts (normally open contacts)		4
Number of auxiliary contacts (normally closed contacts)		0
Number of auxiliary contacts (normally open contacts)		4
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		1 W
Rated operational current for specified heat dissipation (In)		15.5 A
Static heat dissipation, non-current-dependent Pvs		3 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Contactor relay (EC000196)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Contactor (LV) / Contactor relay (ecl@ss10.0.1-27-37-10-01 [AAB716014])		
Rated control supply voltage Us at AC 50HZ	V	0 - 0
Rated control supply voltage Us at AC 60HZ	V	0 - 0
Rated control supply voltage Us at DC	V	24 - 24
Voltage type for actuating		DC
Rated operation current Ie, 400 V	A	4
Connection type auxiliary circuit		Screw connection
Mounting method		DIN-rail/screw
Interface		No
Number of auxiliary contacts as normally closed contact		0
Number of auxiliary contacts as normally open contact		4
Number of auxiliary contacts as normally closed contact, delayed switching		0
Number of auxiliary contacts as normally open contact, leading		0
Number of auxiliary contacts as change-over contact		0
With LED indication		No
Suitable for manual operation		No

