



H.b.c fuse switch strip NH, 250A, 500V/250A, 690V/200A, size 1

Part no. LTS-L/250/1  
 Catalog No. 269350

### Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / In-line fuse base (EC001046)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse strip (ecl@ss8.1-27-37-14-02 [AKF059010])		
Model		Fuse switch disconnecter
Double interrupting		No
Rated permanent current I <sub>u</sub>	A	250
Distance between rail centre, 40 mm		No
Distance between rail centre, 50 mm		No
Distance between rail centre, 60 mm		No
Distance between rail centre, 100 mm		No
Distance between rail centre, 185 mm		Yes
Max. rated operation voltage U <sub>e</sub> AC	V	690
Conditioned rated short-circuit current I <sub>q</sub>	kA	120
Type of electrical connection of main circuit		Screw connection
Number of poles		3
Construction size fuse insert		NH1