

**Auxiliary contact module, 4 pole, Ith= 16 A, 2 N/O, 2 NC, Front fixing,  
Screw terminals, DILM40 - DILM170**

**Part no. DILM150-XHI22**

**277950**

**EL Number**

**4130497**

**(Norway)**

<b>General specifications</b>	
Product name	Eaton Moeller® series DILM auxiliary contact module
Part no.	DILM150-XHI22
EAN	4015082779504
Product Length/Depth	39 millimetre
Product height	46 millimetre
Product width	45 millimetre
Product weight	0.055 kilogram
Certifications	CSA-C22.2 No. 14-05 CSA File No.: 012528 UL File No.: E29184 CE UL Category Control No.: NKCR IEC/EN 60947 UL 508 CSA Class No.: 3211-03 VDE 0660 UL IEC/EN 60947-4-1 CSA
Product Tradename	DILM
Product Type	Accessory
Product Sub Type	Auxiliary contact module
Catalog Notes	Auxiliary contacts used as mirror contacts (according to IEC/EN 60947-4-1 Appendix F (not N/C late open)) Interlocked opposing contacts according to IEC/EN 60947-5-1 Appendix L, inside the auxiliary contact module Rated operational current: Switch-on and switch-off conditions based on DC-13, time constant as specified.
<b>Features &amp; Functions</b>	
Features	Interlocked opposing contacts within an auxiliary contact module (according to IEC 60947-5-1 Annex L)
Functions	For standard applications
Fitted with:	Interlocked opposing contacts
Number of poles	Four-pole
Electric connection type	Screw connection
<b>General information</b>	
Degree of protection	IP20
Lifespan, electrical	1,300,000 Operations (at 230 V, AC-15, 3 A)
Model	Top mounting
Mounting method	Front fastening
Overvoltage category	III
Pollution degree	3
Protection	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
Rated impulse withstand voltage (Uimp)	6000 V AC
Type	Front mounting auxiliary contact
<b>Ambient conditions, mechanical</b>	
Shock resistance	5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
<b>Climatic environmental conditions</b>	
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	60 °C

Ambient operating temperature (enclosed) - min		25 °C
Ambient operating temperature (enclosed) - max		40 °C
Ambient storage temperature - min		40 °C
Ambient storage temperature - max		80 °C
Climatic proofing		Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
<b>Terminal capacities</b>		
Terminal capacity (flexible with ferrule)		2 x (0.75 - 2.5) mm <sup>2</sup> 1 x (0.75 - 2.5) mm <sup>2</sup>
Terminal capacity (solid)		2 x (0.75 - 2.5) mm <sup>2</sup> 1 x (0.75 - 2.5) mm <sup>2</sup>
Terminal capacity (solid/stranded AWG)		18 - 14
Screwdriver size		0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver
Tightening torque		1.2 Nm, Screw terminals
<b>Electrical rating</b>		
Rated operational current (Ie)		6 A at 60 V, DC L/R ≤ 15 ms (with 1 contact in series) 1 A at 220 V, DC L/R ≤ 15 ms (with 1 contact in series) 10 A at 24 V, DC L/R ≤ 15 ms (with 1 contact in series) 3 A at 110 V, DC L/R ≤ 15 ms (with 1 contact in series)
Rated operational current (Ie) at AC-15, 220 V, 230 V, 240 V		6 A
Rated operational current (Ie) at AC-15, 380 V, 400 V, 415 V		4 A
Rated operational current (Ie) at AC-15, 500 V		1.5 A
Rated insulation voltage (Ui)		690 V
Rated operational voltage (Ue) at AC - max		500 V
<b>Short-circuit rating</b>		
Short-circuit protection rating		Max. 16 A gG/gL, Fuse, Without welding, Auxiliary contacts
Short-circuit protection rating without welding		16 A gG/gL, 500 V, Max. Fuse, Contacts
<b>Conventional thermal current Ith</b>		
Conventional thermal current Ith at 60°C (3-pole, open)		16 A
<b>Switching capacity</b>		
Switching capacity (auxiliary contacts, general use)		15 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA)
Switching capacity (auxiliary contacts, pilot duty)		P300, DC operated (UL/CSA) A600, AC operated (UL/CSA)
<b>Communication</b>		
Connection type		Screw connection
<b>Contacts</b>		
Control circuit reliability		< 2 λ, < 1 failure at 100,000,000 Operations (at U# = 24 V DC, Umin = 17 V, Imin = 5.4 mA)
Number of contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		2
Number of contacts (normally open contacts)		2
<b>Safety</b>		
Safe isolation		440 V AC, Between auxiliary contacts, According to EN 61140 440 V AC, Between coil and auxiliary contacts, According to EN 61140
<b>Design verification</b>		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdiss		0 W
Heat dissipation per pole, current-dependent Pvid		0.23 W
Rated operational current for specified heat dissipation (In)		4 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact			Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions			Meets the product standard's requirements.
10.3 Degree of protection of assemblies			Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances			Meets the product standard's requirements.
10.5 Protection against electric shock			Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components			Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections			Is the panel builder's responsibility.
10.8 Connections for external conductors			Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength			Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage			Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material			Is the panel builder's responsibility.
10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Auxiliary contact block (EC000041)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Auxiliary switch block (ecI@ss10.0.1-27-37-13-02 [AKN342013])			
Number of contacts as change-over contact			0
Number of contacts as normally open contact			2
Number of contacts as normally closed contact			2
Number of fault-signal switches			0
Rated operation current I <sub>e</sub> at AC-15, 230 V		A	6
Type of electric connection			Screw connection
Model			Top mounting
Mounting method			Front fastening
Lamp holder			None