

Contactors, 3 pole, 380 V 400 V 3 kW, 1 N/O, 230 V 50 Hz, 240 V 60 Hz, AC operation, Screw terminals



Part no. DILM7-10(230V50HZ,240V60HZ)

276550

EL Number 4130261

(Norway)

General specifications		
Product name		Eaton Moeller® series DILM contactor
Part no.		DILM7-10(230V50HZ,240V60HZ)
EAN		4015082765507
Product Length/Depth		75 millimetre
Product height		68 millimetre
Product width		45 millimetre
Product weight		0.24 kilogram
Certifications		UL File No.: E29096 VDE 0660 UL Category Control No.: NLDX CSA-C22.2 No. 60947-4-1-14 IEC/EN 60947 CE CSA CSA Class No.: 2411-03, 3211-04 UL 60947-4-1 UL CSA File No.: 012528 IEC/EN 60947-4-1
Product Tradename		DILM
Product Type		Contactors
Product Sub Type		None
Catalog Notes		Contacts according to EN 50012
General information		
Application		Contactors for Motors
Degree of protection		IP20
Frame size		FS1
Lifespan, mechanical		10,000,000 Operations (AC operated)
Operating frequency		9000 mechanical Operations/h (AC operated)
Overtoltage category		III
Pollution degree		3
Product category		Contactors
Protection		Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
Rated impulse withstand voltage (Uimp)		8000 V AC
Resistance per pole		2.5 mΩ
Suitable for		Also motors with efficiency class IE3
Utilization category		AC-4: Normal AC induction motors: starting, plugging, reversing, inching AC-1: Non-inductive or slightly inductive loads, resistance furnaces AC-3: Normal AC induction motors: starting, switch off during running
Voltage type		AC
Ambient conditions, mechanical		
Shock resistance		7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 5.7 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 10 g, N/O main contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 3.4 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms 3.4 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27 when tabletop-mounted, Half-sinusoidal shock 10 ms
Climatic environmental conditions		
Altitude		Max. 2000 m

Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		60 °C
Ambient operating temperature (enclosed) - min		25 °C
Ambient operating temperature (enclosed) - max		40 °C
Ambient storage temperature - min		40 °C
Ambient storage temperature - max		80 °C
Climatic proofing		Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
Electro magnetic compatibility		
Emitted interference		According to EN 60947-1
Interference immunity		According to EN 60947-1
Terminal capacities		
Terminal capacity (flexible with ferrule)		2 x (0.75 - 2.5) mm ² 2 x (0.75 - 2,5) mm ² 1 x (0.75 - 2.5) mm ²
Terminal capacity (solid)		1 x (0.75 - 4) mm ² 2 x (0.75 - 2.5) mm ²
Terminal capacity (solid/stranded AWG)		Single 18 - 10, double 18 - 14
Stripping length (main cable)		10 mm
Stripping length (control circuit cable)		10 mm
Screw size		M3.5, Terminal screw
Screwdriver size		0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver 2, Terminal screw, Pozidriv screwdriver
Tightening torque		1.2 Nm, Screw terminals
Electrical rating		
Rated breaking capacity at 220/230 V		70 A
Rated breaking capacity at 380/400 V		70 A
Rated breaking capacity at 500 V		50 A
Rated breaking capacity at 660/690 V		40 A
Rated operational current (Ie) at AC-1, 380 V, 400 V, 415 V		22 A
Rated operational current (Ie) at AC-3, 220 V, 230 V, 240 V		7 A
Rated operational current (Ie) at AC-3, 380 V, 400 V, 415 V		7 A
Rated operational current (Ie) at AC-3, 440 V		7 A
Rated operational current (Ie) at AC-3, 500 V		5 A
Rated operational current (Ie) at AC-3, 660 V, 690 V		4 A
Rated operational current (Ie) at AC-4, 220 V, 230 V, 240 V		5 A
Rated operational current (Ie) at AC-4, 440 V		5 A
Rated operational current (Ie) at AC-4, 500 V		4.5 A
Rated operational current (Ie) at AC-4, 660 V, 690 V		4 A
Rated operational current (Ie) at DC-1, 60 V		20 A
Rated operational current (Ie) at DC-1, 110 V		20 A
Rated operational current (Ie) at DC-1, 220 V		15 A
Rated insulation voltage (Ui)		690 V
Rated making capacity up to 690 V (cos phi to IEC/EN 60947)		112 A
Rated operational power at AC-3, 240 V, 50 Hz		2.2 kW
Rated operational power at AC-3, 380/400 V, 50 Hz		3 kW
Rated operational power at AC-3, 415 V, 50 Hz		4 kW
Rated operational power at AC-3, 440 V, 50 Hz		4.5 kW
Rated operational power at AC-3, 500 V, 50 Hz		3.5 kW
Rated operational power at AC-3, 690 V, 50 Hz		3.5 kW
Rated operational power at AC-4, 220/230 V, 50 Hz		1 kW
Rated operational power at AC-4, 240 V, 50 Hz		1.5 kW
Rated operational power at AC-4, 415 V, 50 Hz		2.3 kW
Rated operational power at AC-4, 440 V, 50 Hz		2.4 kW
Rated operational power at AC-4, 500 V, 50 Hz		2.5 kW
Rated operational power at AC-4, 660/690 V, 50 Hz		2.9 kW
Rated operational voltage (Ue) at AC - max		690 V

Short-circuit rating		
Short-circuit current rating (basic rating)		5 kA, SCCR (UL/CSA) 45 A, max. Fuse, SCCR (UL/CSA) 60 A, max. CB, SCCR (UL/CSA)
Short-circuit current rating (high fault at 480 V)		25 A, Class RK5/ 20 A Class J, max. Fuse, SCCR (UL/CSA) 30/100 kA, Fuse, SCCR (UL/CSA) 65 kA, CB, SCCR (UL/CSA) 16 A, max. CB, SCCR (UL/CSA)
Short-circuit current rating (high fault at 600 V)		30/100 kA, Fuse, SCCR (UL/CSA) 25 A, Class RK5/20 A, Class J, max. Fuse, SCCR (UL/CSA)
Short-circuit protection rating (type 1 coordination) at 400 V		35 A gG/gL
Short-circuit protection rating (type 1 coordination) at 690 V		20 A gG/gL
Short-circuit protection rating (type 2 coordination) at 400 V		20 A gG/gL
Short-circuit protection rating (type 2 coordination) at 690 V		16 A gG/gL
Conventional thermal current I_{th}		
Conventional thermal current I _{th} (1-pole, enclosed)		45 A
Conventional thermal current I _{th} (3-pole, enclosed)		18 A
Conventional thermal current I _{th} at 55°C (3-pole, open)		21 A
Conventional thermal current I _{th} at 60°C (3-pole, open)		20 A
Conventional thermal current I _{th} of main contacts (1-pole, open)		50 A
Switching capacity		
Switching capacity (main contacts, general use)		20 A, Maximum motor rating (UL/CSA)
Switching capacity (auxiliary contacts, general use)		1 A, 250 V DC, (UL/CSA) 10 A, 600 V AC, (UL/CSA)
Switching capacity (auxiliary contacts, pilot duty)		P300, DC operated (UL/CSA) A600, AC operated (UL/CSA)
Magnet system		
Arcing time		10 ms
Drop-out voltage		AC operated: 0.6 - 0.3 x U _C , AC operated
Duty factor		100 %
Pick-up voltage		0.8 - 1.1 V AC x U _C
Power consumption, pick-up, 50 Hz		24 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz
Power consumption, pick-up, 60 Hz		30 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz
Power consumption, sealing, 50 Hz		3.4 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz 1.4 W, Dual-frequency coil in a cold state and 1.0 x U _s , at 50 Hz
Power consumption, sealing, 60 Hz		1.4 W, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz 4.4 VA, Dual-frequency coil in a cold state and 1.0 x U _s , at 60 Hz
Rated control supply voltage (U _s) at AC, 50 Hz - min		230 V
Rated control supply voltage (U _s) at AC, 50 Hz - max		230 V
Rated control supply voltage (U _s) at AC, 60 Hz - min		240 V
Rated control supply voltage (U _s) at AC, 60 Hz - max		240 V
Rated control supply voltage (U _s) at DC - min		0 V
Rated control supply voltage (U _s) at DC - max		0 V
Switching time (AC operated, make contacts, closing delay) - min		15 ms
Switching time (AC operated, make contacts, closing delay) - max		21 ms
Switching time (AC operated, make contacts, opening delay) - min		9 ms
Switching time (AC operated, make contacts, opening delay) - max		18 ms
Motor rating		
Assigned motor power at 115/120 V, 60 Hz, 1-phase		0.25 HP
Assigned motor power at 200/208 V, 60 Hz, 3-phase		1.5 HP
Assigned motor power at 230/240 V, 60 Hz, 1-phase		1 HP
Assigned motor power at 230/240 V, 60 Hz, 3-phase		2 HP
Assigned motor power at 460/480 V, 60 Hz, 3-phase		3 HP
Assigned motor power at 575/600 V, 60 Hz, 3-phase		5 HP
Communication		
Connection		Screw terminals
Connection to SmartWire-DT		No
Contacts		

Number of contacts (normally open contacts)		1
Number of auxiliary contacts (normally closed contacts)		0
Number of auxiliary contacts (normally open contacts)		1
Safety		
Safe isolation		400 V AC, Between the contacts, According to EN 61140 400 V AC, Between coil and contacts, According to EN 61140
Special purpose ratings		
Special purpose rating of ballast electrical discharge lamps		12 A (600V 60Hz 3phase, 347V 60Hz 1phase) 12 A (480V 60Hz 3phase, 277V 60Hz 1phase)
Special purpose rating of definite purpose rating		7 A, FLA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA) 42 A, LRA 480 V 60 Hz 3-ph, 100,000 cycles acc. to UL 1995, (UL/CSA)
Special purpose rating of elevator control		3.7 A, 200 V 60 Hz 3-ph, (UL/CSA) 6 A, 240 V 60 Hz 3-ph, (UL/CSA) 3.4 A, 480 V 60 Hz 3-ph, (UL/CSA) 0.75 HP, 200 V 60 Hz 3-ph, (UL/CSA) 2 HP, 480 V 60 Hz 3-ph, (UL/CSA) 3.9 A, 600 V 60 Hz 3-ph, (UL/CSA) 1.5 HP, 240 V 60 Hz 3-ph, (UL/CSA) 3 HP, 600 V 60 Hz 3-ph, (UL/CSA)
Special purpose rating of refrigeration control (CSA only)		60 A, LRA 600 V 60 Hz 3phase; (CSA) 60 A, LRA 480 V 60 Hz 3phase; (CSA) 10 A, FLA 480 V 60 Hz 3phase; (CSA) 10 A, FLA 600 V 60 Hz 3phase; (CSA)
Special purpose rating of resistance air heating		12 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA) 12 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA)
Special purpose rating of tungsten incandescent lamps		14 A, 600 V 60 Hz 3phase, 347 V 60 Hz 1phase, (UL/CSA) 14 A, 480 V 60 Hz 3phase, 277 V 60 Hz 1phase, (UL/CSA)
Design verification		
Equipment heat dissipation, current-dependent P _{vid}		0 W
Heat dissipation capacity P _{diss}		0 W
Heat dissipation per pole, current-dependent P _{vid}		0.1 W
Rated operational current for specified heat dissipation (I _n)		7 A
Static heat dissipation, non-current-dependent P _{vs}		1.4 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Power contactor, AC switching (EC000066)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Contactor (LV) / Power contactor, AC switching (ecl@ss10.0.1-27-37-10-03 [AAB718015])		
Rated control supply voltage U _s at AC 50HZ	V	230 - 230

Rated control supply voltage U_s at AC 60HZ	V	240 - 240
Rated control supply voltage U_s at DC	V	0 - 0
Voltage type for actuating		AC
Rated operation current I_e at AC-1, 400 V	A	22
Rated operation current I_e at AC-3, 400 V	A	7
Rated operation power at AC-3, 400 V	kW	3
Rated operation current I_e at AC-4, 400 V	A	5
Rated operation power at AC-4, 400 V	kW	2.2
Rated operation power NEMA	kW	2.2
Modular version		No
Number of auxiliary contacts as normally open contact		1
Number of auxiliary contacts as normally closed contact		0
Type of electrical connection of main circuit		Screw connection
Number of normally closed contacts as main contact		0
Number of normally open contacts as main contact		3