





**Overload relay, 10-16A, 1N/O+1N/C**

**Part no.** ZB65-16  
**Catalog No.** 278456  
**Eaton Catalog No.** XTOB016DC1  
**EL-Nummer (Norway)** 0004131851

**Delivery program**

|  |       |   |  |
|--|-------|---|--|
| Product range  |       |   | Overload relay ZB up to 150 A  |
| Product range  |       |   | Accessories  |
| Accessories  |       |   | Overload relays  |
| Frame size   |       |   | ZB65   |
| Phase-failure sensitivity  |       |   | IEC/EN 60947, VDE 0660 Part 102  |
| Description  |       |   | Test/off button<br>Reset pushbutton manual/auto<br>Trip-free release   |
| Mounting type  |       |   | Direct mounting  |
|                              | $I_r$ | A | 10 - 16  |
| Contact sequence   |       |   |    |
| <b>Auxiliary contacts</b>  |       |   |  |
| N/O = Normally open  |       |   | 1 N/O  |
| N/C = Normally closed  |       |   | 1 N/C  |
| For use with   |       |   | DILM40<br>DILM50<br>DILM65<br>DILM72<br>DILMF40<br>DILMF50<br>DILMF65<br>DIULM40<br>DIULM50<br>DIULM65<br>SDAINLM70<br>SDAINLM90<br>SDAINLM115 |
| <b>Short-circuit protection</b>  |       |   |  |
| Type "1" coordination<br> | gG/gL | A | 63   |
| Type "2" coordination<br> | gG/gL | A | 35   |

**Notes**

Overload trigger: tripping class 10 A

Short circuit protection: observe the maximum permissible fuse of the contactor with direct device mounting.

Suitable for protection of Ex e-motors.




II(2)G [Ex d] [Ex e] [Ex px], II(2)D [Ex p] [Ex t]


PTB 10 ATEX 3010

**Notes**

Fitted directly to the contactor



Separate mounting



1 Contactor  
2 Bases

**Technical data**

**General**

|   |    |  |  |
|---|----|--|--|
| Standards   |    |  | IEC/EN 60947, VDE 0660, UL, CSA  |
| Climatic proofing   |    |  | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30 |
| Ambient temperature   |    |  | Operating range to IEC/EN 60947<br>PTB: -5 °C - +55 °C                         |
| Open  | °C |  | -25 - +55  |
| Enclosed  | °C |  | -25 - 40   |
| Temperature compensation  |    |  | Continuous   |
| Weight  | kg |  | 0.22   |
| Mechanical shock resistance   | g  |  | 10<br>Sinusoidal<br>Shock duration 10 ms                                       |
| Degree of Protection  |    |  | IP00   |
| Protection against direct contact when actuated from front (EN 50274) |    |  | Finger and back-of-hand proof  |

**Main conducting paths**

|  |           |                 |                              |
|--|-----------|-----------------|------------------------------|
| Rated impulse withstand voltage                | $U_{imp}$ | V AC            | 6000                         |
| Overvoltage category/pollution degree          |           |                 | III/3                        |
| Rated insulation voltage                       | $U_i$     | V               | 690                          |
| Rated operational voltage                      | $U_e$     | V AC            | 690                          |
| Safe isolation to EN 61140                     |           |                 |                              |
| Between auxiliary contacts and main contacts   |           | V AC            | 440                          |
| Between main circuits                          |           | V AC            | 440                          |
| Temperatur compensation residual error > 40 °C |           |                 | $\leq 0.25 \%/K$             |
| Current heat loss (3 conductors)               |           |                 |                              |
| Lower value of the setting range               |           | W               | 2.5                          |
| Maximum setting                                |           | W               | 6.3                          |
| Terminal capacities                            |           | mm <sup>2</sup> |                              |
| Solid  |           | mm <sup>2</sup> | 1 x (1 - 16)<br>2 x (1 - 16) |
| Flexible with ferrule                          |           | mm <sup>2</sup> | 1 x (1 - 25)<br>2 x (1 - 25) |
| Stranded                                       |           | mm <sup>2</sup> | 1 x (16 - 25)                |
| Solid or stranded                              |           | AWG             | 14 - 2                       |
| Terminal screw                                 |           |                 | M6                           |
| Tightening torque                              |           | Nm              | 3.5                          |
| Stripping length                               |           | mm              | 11                           |

|                      |  |      |       |
|----------------------|--|------|-------|
| Tools                |  |      |       |
| Pozidriv screwdriver |  | Size | 2     |
| Standard screwdriver |  | mm   | 1 x 6 |

### Auxiliary and control circuits

|                                       |           |         |   |
|---------------------------------------|-----------|---------|---|
| Rated impulse withstand voltage       | $U_{imp}$ | V       | 4000  |
| Overvoltage category/pollution degree |           |         | III/3   |
| Terminal capacities                   |           | $mm^2$  |   |
| Solid                                 |           | $mm^2$  | 1 x (0.75 - 4)<br>2 x (0.75 - 4)  |
| Flexible with ferrule                 |           | $mm^2$  | 1 x (0.75 - 2.5)<br>2 x (0.75 - 2.5)  |
| Solid or stranded                     |           | AWG     | 2 x (18 - 14)   |
| Terminal screw                        |           |         | M3.5  |
| Tightening torque                     |           | Nm      | 1.2   |
| Stripping length                      |           | mm      | 8   |
| Tools                                 |           |         |   |
| Pozidriv screwdriver                  |           | Size    | 2   |
| Standard screwdriver                  |           | mm      | 1 x 6   |
| Rated insulation voltage              | $U_i$     | V AC    | 500   |
| Rated operational voltage             | $U_e$     | V AC    | 500   |
| Safe isolation to EN 61140            |           |         |   |
| between the auxiliary contacts        |           | V AC    | 240   |
| Conventional thermal current          | $I_{th}$  | A       | 6   |
| Rated operational current             | $I_e$     | A       |   |
| AC-15                                 |           |         |   |
| Make contact                          |           |         |   |
| 120 V                                 | $I_e$     | A       | 1.5   |
| 220 V 230 V 240 V                     | $I_e$     | A       | 1.5   |
| 380 V 400 V 415 V                     | $I_e$     | A       | 0.5   |
| 500 V                                 | $I_e$     | A       | 0.5   |
| Break contact                         |           |         |   |
| 120 V                                 | $I_e$     | A       | 1.5   |
| 220 V 230 V 240 V                     | $I_e$     | A       | 1.5   |
| 380 V 400 V 415 V                     | $I_e$     | A       | 0.9   |
| 500 V                                 | $I_e$     | A       | 0.8   |
| DC L/R $\leq$ 15 ms                   |           |         |   |
|                                       |           |         | Switch-on and switch-off conditions based on DC-13, time constant as specified. |
| 24 V                                  | $I_e$     | A       | 0.9   |
| 60 V                                  | $I_e$     | A       | 0.75  |
| 110 V                                 | $I_e$     | A       | 0.4   |
| 220 V                                 | $I_e$     | A       | 0.2   |
| Short-circuit rating without welding  |           |         |   |
| max. fuse                             |           | A gG/gL | 6   |

### Notes

**Notes** Ambient air temperature: Operating range to IEC/EN 60947, PTB: -5°C to +55°C  
Main circuits terminal capacity solid and flexible conductors with ferrules: When using 2 conductors use equal cross-sections.

### Rating data for approved types

|                              |  |    |  |
|------------------------------|--|----|--|
| Auxiliary contacts           |  |    |  |
| Pilot Duty                   |  |    |  |
| AC operated                  |  |    | B300 at opposite polarity<br>B600 at same polarity |
| DC operated                  |  |    | R300   |
| Short Circuit Current Rating |  |    |  |
| Basic Rating                 |  |    |  |
| SCCR                         |  | kA | 5  |
| max. Fuse                    |  | A  | 60   |

|                  |    |               |
|------------------|----|---------------|
| max. CB          | A  | 60            |
| 480 V High Fault |    |               |
| SCCR (fuse)      | kA | 100           |
| max. Fuse        | A  | 35 Class J/CC |
| SCCR (CB)        | kA | 65            |
| max. CB          | A  | 25            |
| 600 V High Fault |    |               |
| SCCR (fuse)      | kA | 100           |
| max. Fuse        | A  | 35 Class J/CC |

## Design verification as per IEC/EN 61439

|  |            |    |  |
|--|------------|----|--|
| Technical data for design verification   |            |    |  |
| Rated operational current for specified heat dissipation   | $I_n$      | A  | 16   |
| Heat dissipation per pole, current-dependent   | $P_{vid}$  | W  | 2.1  |
| Equipment heat dissipation, current-dependent  | $P_{vid}$  | W  | 6.3  |
| Static heat dissipation, non-current-dependent   | $P_{vs}$   | W  | 0  |
| Heat dissipation capacity  | $P_{diss}$ | W  | 0  |
| Operating ambient temperature min.   |            | °C | -25  |
| Operating ambient temperature max.   |            | °C | 55   |
| IEC/EN 61439 design verification   |            |    |  |
| 10.2 Strength of materials and parts   |            |    |  |
| 10.2.2 Corrosion resistance  |            |    | Meets the product standard's requirements.   |
| 10.2.3.1 Verification of thermal stability of enclosures   |            |    | Meets the product standard's requirements.   |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat   |            |    | Meets the product standard's requirements.   |
| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects |            |    | Meets the product standard's requirements.   |
| 10.2.4 Resistance to ultra-violet (UV) radiation   |            |    | Meets the product standard's requirements.   |
| 10.2.5 Lifting   |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.2.6 Mechanical impact   |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.2.7 Inscriptions  |            |    | Meets the product standard's requirements.   |
| 10.3 Degree of protection of ASSEMBLIES  |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.4 Clearances and creepage distances   |            |    | Meets the product standard's requirements.   |
| 10.5 Protection against electric shock   |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.6 Incorporation of switching devices and components   |            |    | Does not apply, since the entire switchgear needs to be evaluated.   |
| 10.7 Internal electrical circuits and connections  |            |    | Is the panel builder's responsibility.   |
| 10.8 Connections for external conductors   |            |    | Is the panel builder's responsibility.   |
| 10.9 Insulation properties   |            |    |  |
| 10.9.2 Power-frequency electric strength   |            |    | Is the panel builder's responsibility.   |
| 10.9.3 Impulse withstand voltage   |            |    | Is the panel builder's responsibility.   |
| 10.9.4 Testing of enclosures made of insulating material   |            |    | Is the panel builder's responsibility.   |
| 10.10 Temperature rise   |            |    | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 Short-circuit rating   |            |    | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.12 Electromagnetic compatibility  |            |    | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| 10.13 Mechanical function  |            |    | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |

## Technical data ETIM 7.0


|  |   |                   |  |
|--|---|-------------------|--|
| Low-voltage industrial components (EG000017) / Thermal overload relay (EC000106)   |   |                   |  |
| Electric engineering, automation, process control engineering / Low-voltage switch technology / Overload protection device / Thermal overload relay (ecl@ss10.0.1-27-37-15-01 [AKF075014]) |   |                   |  |
| Adjustable current range   | A | 10 - 16           |  |
| Max. rated operation voltage $U_e$   | V | 690               |  |
| Mounting method  |   | Direct attachment |  |
| Type of electrical connection of main circuit  |   | Screw connection  |  |
| Number of auxiliary contacts as normally closed contact  |   | 1                 |  |

|   |  |  |          |
|---|--|--|----------|
| Number of auxiliary contacts as normally open contact |  |  | 1        |
| Number of auxiliary contacts as change-over contact   |  |  | 0        |
| Release class   |  |  | CLASS 10 |
| Reset function input                                  |  |  | No       |
| Reset function automatic                              |  |  | Yes      |
| Reset function push-button                            |  |  | Yes      |

## Approvals



|                                      |  |  |  |
|--------------------------------------|--|--|--|
| Product Standards                    |  |  | IEC/EN 60947-4-1; UL 60947-4-1; CSA - C22.2 No. 60947-4-1-14; CE marking |
| UL File No.                          |  |  | E29184   |
| UL Category Control No.              |  |  | NKCR   |
| CSA File No.                         |  |  | 12528  |
| CSA Class No.                        |  |  | 3211-03  |
| North America Certification          |  |  | UL listed, CSA certified   |
| Specially designed for North America |  |  | No   |
| Suitable for                         |  |  | Branch circuits  |
| Max. Voltage Rating                  |  |  | 600 V AC   |
| Degree of Protection                 |  |  | IEC: IP00, UL/CSA Type: -  |

## Characteristics





These tripping characteristics are mean values of the spread at 20 °C ambient temperature in a cold state. Tripping time depends on response current. On devices at operating temperature the tripping time of the overload relay drops to approx. 25 % of the read value. Specific characteristics for each individual setting range can be found in the manual.

# Dimensions



- ① OFF
- ② Reset/ON



With base ZB65-XEZ

## Additional product information (links)

### IL03407008Z (AWA2300-2113) Overload relay

IL03407008Z (AWA2300-2113) Overload relay [ftp://ftp.moeller.net/DOCUMENTATION/AWA\\_INSTRUCTIONS/IL03407008Z2018\\_03.pdf](ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL03407008Z2018_03.pdf)

### MN03407005Z (AWB2300-1545) ZB65 and ZB150 overload relays - overload monitoring of Ex e motors

MN03407005Z (AWB2300-1545) ZB65 and ZB150 overload relays - overload monitoring of Ex e motors - Deutsch / English [ftp://ftp.moeller.net/DOCUMENTATION/AWB\\_MANUALS/MN03407005Z\\_DE\\_EN.pdf](ftp://ftp.moeller.net/DOCUMENTATION/AWB_MANUALS/MN03407005Z_DE_EN.pdf)