

**Auxiliary contact module, 4 pole, Ith= 16 A, 3 N/O, 1 NC, Front fixing,
Screw terminals, DILM40 - DILM170**

Part no. DILM150-XHI31
277949

EL Number
(Norway) 4130498

General specifications		
Product name		Eaton Moeller® series DILM auxiliary contact module
Part no.		DILM150-XHI31
EAN		4015082779498
Product Length/Depth		39 millimetre
Product height		46 millimetre
Product width		45 millimetre
Product weight		0.055 kilogram
Certifications		UL Category Control No.: NKCR VDE 0660 CSA File No.: 012528 IEC/EN 60947-4-1 UL 508 UL UL File No.: E29184 IEC/EN 60947 CSA CSA Class No.: 3211-03 CE CSA-C22.2 No. 14-05
Product Tradename		DILM
Product Type		Accessory
Product Sub Type		Auxiliary contact module
Catalog Notes		Auxiliary contacts used as mirror contacts (according to IEC/EN 60947-4-1 Appendix F (not N/C late open)) Interlocked opposing contacts according to IEC/EN 60947-5-1 Appendix L, inside the auxiliary contact module Rated operational current: Switch-on and switch-off conditions based on DC-13, time constant as specified.
Features & Functions		
Features		Interlocked opposing contacts within an auxiliary contact module (according to IEC 60947-5-1 Annex L)
Functions		For standard applications
Fitted with:		Interlocked opposing contacts
Number of poles		Four-pole
Electric connection type		Screw connection
General information		
Degree of protection		IP20
Lifespan, electrical		1,300,000 Operations (at 230 V, AC-15, 3 A)
Model		Top mounting
Mounting method		Front fastening
Overvoltage category		III
Pollution degree		3
Protection		Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
Rated impulse withstand voltage (Uimp)		6000 V AC
Type		Front mounting auxiliary contact
Ambient conditions, mechanical		
Shock resistance		5 g, N/C auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms 7 g, N/O auxiliary contact, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		60 °C

Ambient operating temperature (enclosed) - min		25 °C
Ambient operating temperature (enclosed) - max		40 °C
Ambient storage temperature - min		40 °C
Ambient storage temperature - max		80 °C
Climatic proofing		Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
Terminal capacities		
Terminal capacity (flexible with ferrule)		2 x (0.75 - 2.5) mm ² 1 x (0.75 - 2.5) mm ²
Terminal capacity (solid)		2 x (0.75 - 2.5) mm ² 1 x (0.75 - 2.5) mm ²
Terminal capacity (solid/stranded AWG)		18 - 14
Screwdriver size		2, Terminal screw, Pozidriv screwdriver 0.8 x 5.5/1 x 6 mm, Terminal screw, Standard screwdriver
Tightening torque		1.2 Nm, Screw terminals
Electrical rating		
Rated operational current (Ie)		6 A at 60 V, DC L/R ≤ 15 ms (with 1 contact in series) 10 A at 24 V, DC L/R ≤ 15 ms (with 1 contact in series) 3 A at 110 V, DC L/R ≤ 15 ms (with 1 contact in series) 1 A at 220 V, DC L/R ≤ 15 ms (with 1 contact in series)
Rated operational current (Ie) at AC-15, 220 V, 230 V, 240 V		6 A
Rated operational current (Ie) at AC-15, 380 V, 400 V, 415 V		4 A
Rated operational current (Ie) at AC-15, 500 V		1.5 A
Rated insulation voltage (Ui)		690 V
Rated operational voltage (Ue) at AC - max		500 V
Short-circuit rating		
Short-circuit protection rating		Max. 16 A gG/gL, Fuse, Without welding, Auxiliary contacts
Short-circuit protection rating without welding		16 A gG/gL, 500 V, Max. Fuse, Contacts
Conventional thermal current Ith		
Conventional thermal current Ith at 60°C (3-pole, open)		16 A
Switching capacity		
Switching capacity (auxiliary contacts, general use)		1 A, 250 V DC, (UL/CSA) 15 A, 600 V AC, (UL/CSA)
Switching capacity (auxiliary contacts, pilot duty)		A600, AC operated (UL/CSA) P300, DC operated (UL/CSA)
Communication		
Connection type		Screw connection
Contacts		
Control circuit reliability		< 2 λ, < 1 failure at 100,000,000 Operations (at U# = 24 V DC, Umin = 17 V, Imin = 5.4 mA)
Number of contacts (change-over contacts)		0
Number of contacts (normally closed contacts)		1
Number of contacts (normally open contacts)		3
Safety		
Safe isolation		440 V AC, Between coil and auxiliary contacts, According to EN 61140 440 V AC, Between auxiliary contacts, According to EN 61140
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		0.23 W
Rated operational current for specified heat dissipation (In)		4 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Auxiliary contact block (EC000041)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Component for low-voltage switching technology / Auxiliary switch block (ecI@ss10.0.1-27-37-13-02 [AKN342013])		
Number of contacts as change-over contact		0
Number of contacts as normally open contact		3
Number of contacts as normally closed contact		1
Number of fault-signal switches		0
Rated operation current I _e at AC-15, 230 V	A	6
Type of electric connection		Screw connection
Model		Top mounting
Mounting method		Front fastening
Lamp holder		None