

Wiring kit, three-pointed star for DILM7-15



Part no. DILM12-XSL
283130
EL Number 4131899
(Norway)

General specifications	
Product name	Eaton Moeller® series DILM wiring kit
Part no.	DILM12-XSL
EAN	4015082831301
Product Length/Depth	90 millimetre
Product height	20 millimetre
Product width	30 millimetre
Product weight	0.04 kilogram
Certifications	CE CSA-C22.2 No. 14-05 UL 508 CSA File No.: 012528 CSA CSA Class No.: 3211-05 IEC/EN 60947-4-1
Product Tradename	DILM
Product Type	Accessory
Product Sub Type	Wiring kit
Features & Functions	
Fitted with:	Star-point bridge
General information	
Model	Star-delta switching
Product category	Accessories
Climatic environmental conditions	
Ambient operating temperature - min	-25 °C
Ambient operating temperature - max	60 °C
Design verification	
Equipment heat dissipation, current-dependent Pvid	6.6 W
Heat dissipation capacity Pdis	0 W
Heat dissipation per pole, current-dependent Pvid	2.2 W
Rated operational current for specified heat dissipation (In)	22 A
Static heat dissipation, non-current-dependent Pvs	0 W
10.2.2 Corrosion resistance	Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures	Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat	Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects	Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation	Meets the product standard's requirements.
10.2.5 Lifting	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions	Meets the product standard's requirements.
10.3 Degree of protection of assemblies	Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances	Meets the product standard's requirements.
10.5 Protection against electric shock	Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components	Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections	Is the panel builder's responsibility.
10.8 Connections for external conductors	Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength	Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage	Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material	Is the panel builder's responsibility.

10.10 Temperature rise			The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility			Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 8.0

Low-voltage industrial components (EG000017) / Wiring set for power circuit breaker (EC002050)			
Electric engineering, automation, process control engineering / Low-voltage switch technology / Circuit breaker (LV < 1 kV) / Wiring set for circuit breaker (ecl@ss10.0.1-27-37-04-24 [ACN957011])			
Suitable for number of poles			3
Model			Star-delta switching