



Motor fuse-link, medium voltage, 125 A, AC 7.2 kV, 40 kA, 76 x 403 mm, back-up, BS, with striker

Part no. 7.2KV 125A MOTOR START FUSE
Catalog No. 7.2WFNHA125

Similar to illustration

Delivery program

Product range			Fuse
Basic function			Motor fuse-link
Field of application			medium voltage
Rated current	I	A	125
Rated voltage			AC 7.2 kV
Size			76 x 403 mm
Utilization category			back-up
Status indicator			with striker
Breaking Capacity		kA	40
usable for size/applications			motor protection
Standard/Approval			BS
Shape			cylindrical
Standards/Regulations			BS2692-1 IEC 60282-1

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Medium-/high voltage fuse (EC003507)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Safety fuse systems (unspecified) (ecl@ss10.0.1-27-14-21-90 [BAB265011])			
Rated current		A	125
Rated voltage		kV	7.2
Voltage type			AC
Rated frequency		Hz	50 - 50
Breaking capacity		kA	40
Utilization category			Other
Application			Motor protection
Length		mm	403
Diameter		mm	76
Performance category according to IEC 60282-1			Back-up
With striker			Yes
Standard			British Standard
Release characteristic			Other
Installation technique			Air

Additional product information (links)

Product datasheet (pdf)	http://www1.cooperbusmann.com/pdf/4c55bf59-424e-4973-bb95-bd162228cca8.pdf
-------------------------	---