

DATASHEET - 1P+N 22X58 FUSE HOLDER



Fuse holder, low voltage, 125 A, AC 690 V, 22 x 58 mm, 1P + N, IEC, UL



Part no. **1P+N 22x58 Fuse Holder**
Catalog No. **CH221DNU**

Delivery program

| | | | |
|-----------------------|---|---|--------------------|
| Product range | | | Fuse |
| Basic function | | | Fuse-holder |
| Field of application | | | low voltage |
| Rated current | I | A | 125 |
| Rated voltage | | | AC 690 V |
| Size | | | 22 x 58 mm |
| Number of poles | | | 1P + N |
| Standard/Approval | | | IEC UL |
| Standards/Regulations | | | IEC 60269-2 EAC |

Technical data ETIM 8.0

| | | |
|--|----|----------|
| Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705) | | |
| Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007]) | | |
| Nominal voltage | V | 690 |
| Mounting method | | DIN rail |
| For fuse size | | 22x58 mm |
| Number of poles | | 1 |
| Concurrently switching neutral conductor | | No |
| Lockable | | Yes |
| With optical defect indication | | No |
| Width in number of modular spacings | | 4 |
| Built-in depth | mm | 51.5 |
| Degree of protection (IP) | | IP20 |