



**Surface mounted service distribution board**

**Part no.** BP-O-600/10-IVS  
**Catalog No.** 111357



**Delivery program**

Product range			Service distribution board IVS
Basic function			Wall-mounting distribution system
Single unit/Complete unit			Complete housing
Degree of Protection			IP30 (only with door)
Description			Profi Plus basic enclosures Module design, can be dismantled completely Exchangeable door hinges
Material			Sheet steel
Surface finish			Polyester powder coating Phosphated RAL 7035, light grey
Colour			light gray (RAL 7035)
Information about equipment supplied			including base frame, side panels, bottom/top panels and door Including support frame for the IVS mounting units including insulating surround and mounted insulated support bracket including cable entry at top, with push-through flange
Width		mm	600
Height		mm	1060
Depth		mm	262

**Technical data**

**General**

Standards			EN 60439-1/3 IEC 62208
Protection class			1
Degree of Protection			IP30 (only with door)
Power loss			
Max. admissible heat dissipation, ambient air temperature +35 °C		W	147
Weight		kg	28.9

**Material characteristics**

Material			Sheet steel
Surface treatment			Painting, phosphated and polyester powder coating
Surface finish			Polyester powder coating Phosphated RAL 7035, light grey
Colour			light gray (RAL 7035)
Material characteristics			
Type Door			Doors with covered hinges Can be removed from 90°
door opening angle			167° (single mounting) 60° (combination mounting)
Door interlock			Hinge handle with three-point turn-lock Cylinder lock

**Material properties**

Mechanical			
Impact resistance			IK07
Cable entry			Various covers allow cable entry from above and/or below
Electrical			
Rated operational voltage	U <sub>e</sub>	V	690
Rated frequency	f	Hz	50
Rated operational current	I <sub>e</sub>	A	630
Max. admissible heat dissipation, ambient air temperature +35 °C		W	147

Earthings			M5 earthing point screw (base frame) M5 self-tapping screw (enclosure side plate, top/bottom panel) M6 weld stud (door)
-----------	--	--	---

## Design verification as per IEC/EN 61439

Technical data for design verification			
Heat dissipation, at an ambient temperature of 35°C, delta T: 20 degrees in top of the enclosure, calculated as per IEC 60890			
Individual enclosure for wall mounting	P <sub>V</sub>	CO	70
Starting enclosure for wall mounting	P <sub>V</sub>	CO	67
Middle enclosure for wall mounting	P <sub>V</sub>	CO	65
Heat dissipation, at an ambient temperature of 35°C, delta T: 35 degrees in top of the enclosure, calculated as per IEC 60890			
Individual enclosure for wall mounting	P <sub>V</sub>	CO	140
Starting enclosure for wall mounting	P <sub>V</sub>	CO	134
Middle enclosure for wall mounting	P <sub>V</sub>	CO	130
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			
10.2.2.1 Verification of thermal stability of enclosures			
10.2.2.2 Verification of resistance of insulating materials to normal heat			
10.2.2.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			
10.2.4 Resistance to ultra-violet (UV) radiation			
10.2.5 Lifting			
10.2.6 Mechanical impact			
10.2.7 Inscriptions			
10.3 Degree of protection of ASSEMBLIES			
10.4 Clearances and creepage distances			
10.5 Protection against electric shock			
10.6 Incorporation of switching devices and components			
10.7 Internal electrical circuits and connections			
10.8 Connections for external conductors			
10.9 Insulation properties			
10.9.2 Power-frequency electric strength			
10.9.3 Impulse withstand voltage			
10.9.4 Testing of enclosures made of insulating material			
10.10 Temperature rise			
10.11 Short-circuit rating			
10.12 Electromagnetic compatibility			
10.13 Mechanical function			