



Fuse-link, 14x51 mm, 20A, gG

Part no. Z-C14/SE-20A/GG
 Catalog No. 112174

Similar to illustration

Delivery program

Product range			Fuse material
Basic function			Accessories
Basic function			Cylindrical fuse inserts
Utilization category			Utilization category gG (gL)
Size			14 x 51
Rated operational current	I_e	A	20
Rated operational voltage	U_e	V AC	690

Technical data

Electrical

Standards			IEC 60269-1 IEC 60269-2-1
Rated operational voltage	U_e	V	
Rated operational voltage	U_e	V AC	690
	U_e	V AC	
Rated operating voltage	U_e	V AC	2 - 32 A: 690 40 - 50 A: 500
Rated frequency	f	Hz	50

Design verification as per IEC/EN 61439

Technical data for design verification			
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	55

Technical data ETIM 5.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss8-27-14-20-02 [AFZ797009])			
Size			14x51 mm
Rated voltage			AC 690 V
Nominal current		A	20
With striker			No