

Miniature circuit breaker (MCB), 100A, 3p, C-Char, AC

Part no. **PLHT-C100/3**
248040

General specifications		
Product name		Eaton Moeller series xPole - PLHT/-V MCB
Part no.		PLHT-C100/3
EAN		4015082480400
Product Length/Depth		90 millimetre
Product height		75 millimetre
Product width		81 millimetre
Product weight		0.69 kilogram
Compliances		RoHS conform
Product Tradename		xPole - PLHT/-V
Product Type		MCB
Product Sub Type		None
Delivery program		
Application		Switchgear for industrial and advanced commercial applications
Number of poles		Three-pole
Number of poles (total)		3
Number of poles (protected)		3
Tripping characteristic		C
Release characteristic		C
Amperage Rating		100 A
Type		Miniature circuit breaker PLHT
Technical Data - Electrical		
Voltage type		AC
Rated operational voltage (Ue) - max		400 V
Rated insulation voltage (Ui)		440 V
Rated impulse withstand voltage (Uimp)		4 kV
Frequency rating - min		50 Hz
Frequency rating - max		60 Hz
Rated switching capacity (IEC/EN 60947-2)		20 kA
Rated short-circuit breaking capacity (EN 60898) at 230 V		0 kA
Rated short-circuit breaking capacity (EN 60898) at 400 V		0 kA
Rated short-circuit breaking capacity (IEC 60947-2) at 230 V		20 kA
Rated short-circuit breaking capacity (IEC 60947-2) at 400 V		20 kA
Overvoltage category		III
Pollution degree		2
Technical Data - Mechanical		
Width in number of modular spacings		4.5
Built-in depth		75 mm
Degree of protection		IP20
Connectable conductor cross section (solid-core) - min		2.5 mm ²
Connectable conductor cross section (solid-core) - max		50 mm ²
Connectable conductor cross section (multi-wired) - min		2.5 mm ²
Connectable conductor cross section (multi-wired) - max		50 mm ²
Design verification as per IEC/EN 61439 - technical data		
Rated operational current for specified heat dissipation (In)		100 A
Heat dissipation per pole, current-dependent		0 W
Equipment heat dissipation, current-dependent		27.4 W

Static heat dissipation, non-current-dependent		0 W
Heat dissipation capacity		0 W
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		55 °C
Design verification as per IEC/EN 61439		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
Additional information		
Current limiting class		3
Features		Additional equipment possible
Special features		Ambient temperature hint: a 1 °C increase results in a 0.35% linear reduction of current carrying capacity
Used with		Miniature circuit breaker PLHT

Technical data ETIM 8.0

Appareils de protection des installations, des équipements et des personnes (EG000020) / Disjoncteur (EC000042)		
Electricité, Electronique, Automatisation et Commande / Installation électrique, appareillage / Système de disjoncteur modulaire (MCB) / Disjoncteur modulaire (MCB) (ecl@ss10.0.1-27-14-19-01 [AAB905014])		
Built-in depth	mm	75
Release characteristic		C
Number of poles (total)		3
Number of protected poles		3
Rated current	A	100
Rated voltage	V	400
Rated insulation voltage Ui	V	440
Rated impulse withstand voltage Uimp	kV	4
Rated short-circuit breaking capacity Icn according to EN 60898 at 230 V	kA	0
Voltage type		AC
Rated short-circuit breaking capacity Icn according to EN 60898 at 400 V	kA	0
Rated short-circuit breaking capacity Icu according to IEC 60947-2 at 230 V	kA	20
Rated short-circuit breaking capacity Icu according to IEC 60947-2 at 400 V	kA	20
Frequency	Hz	50 - 60
Current limiting class		3
Flush-mounted installation		No

Concurrently switching neutral conductor			No
Over voltage category			3
Pollution degree			2
Additional equipment possible			Yes
Width in number of modular spacings			4.5
Degree of protection (IP)			IP20
Ambient temperature during operating		°C	-25 - 55
Connectable conductor cross section multi-wired		mm ²	2.5 - 50
Connectable conductor cross section solid-core		mm ²	2.5 - 50
Explosion-proof			No