



Fuse-link, high speed, 63 A, AC 690 V, DC 500 V, BS88, 18 x 96 mm, aR, BS

63AFE

Product name		Eaton Bussmann series high speed British standard fuse
Part no.		63AFE
EAN		5027590484961
Product Length/Depth		100 millimetre
Product height		22 millimetre
Product width		187 millimetre
Product weight		45.8 gram
Compliances		CE
Product Tradename		None
Product Type		High speed British standard fuse
Product Sub Type		None
Amperage Rating		63 A
Voltage rating		690 V
Rated voltage AC		690 V
Rated voltage DC		500 V
Class		Class aR
Watt losses		18.5 W
Application		Semiconductor, DC Common bus, DC drives, power converters/rectifiers
Fuse indicator		None

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / HRC fuse (EC004556)		
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Safety fuse inserts (unspecified) (ecl@ss10.0.1-27-14-20-90 [BAB264011])		
Fuse construction type according to IEC 60269		Other
Type of current		AC/DC
Rated voltage AC	V	690
Rated voltage DC	V	500
Rated current	A	63
Utilization category		aR (accompanied semiconductor protection)
Breaking capacity	kA	200
Colour code		None
Type of fuse status indicator		None
Power loss at rated current	W	18.5
Mounting holes		M8
Centre-to-centre distance of connections	mm	76