



Circuit limiter, low voltage, 400 A, DC 80 V, 2.7 kA, 22.2 x 81 mm, UL



**Part no.** ANL CURRENT LIMITER FUSE - 400 AMP  
**Catalog No.** ANL-400

## Delivery program

Product range			Fuse
Basic function			circuit limiter
Field of application			low voltage
Rated current	I	A	400
Rated voltage			DC 80 V
Size			22.2 x 81 mm
Breaking Capacity		kA	2.7
usable for size/applications			fork-lift trucks, marine and other battery-operated systems
Standard/Approval			UL
Optional accessories			fuse-block 4164

## Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse (EC000055)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Low-Voltage HRC fuse (ecl@ss10.0.1-27-14-20-05 [AFZ800015])			
Construction size			Other
Rated current		A	400
Rated voltage		V	80
Voltage type			DC
Rated switching capacity		kA	2.7
Utilization category			Other
Type of fuse status indicator			None
Insulated metal gripping lugs (IMGL)			No

## Additional product information (links)

Product datasheet (pdf)	<a href="http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-a/Bus_Ele_DS_2024_ANL.pdf">http://www.cooperindustries.com/content/dam/public/bussmann/Electrical/Resources/product-datasheets-a/Bus_Ele_DS_2024_ANL.pdf</a>
Product datasheet (web)	<a href="http://www.cooperindustries.com/content/public/en/bussmann/edison/products/special_purpose_fuses/limiters/low-voltage_limiternon-time-delay.html">http://www.cooperindustries.com/content/public/en/bussmann/edison/products/special_purpose_fuses/limiters/low-voltage_limiternon-time-delay.html</a>