

# DATASHEET - 3P+N 14X51 MICRO SWITCH FUSE HOLDER



Fuse holder, low voltage, 50 A, AC 690 V, 14 x 51 mm, 3P + N, IEC, with microswitch, replaces CH143BNMS-F



Part no. **3P+N 14x51 Micro Switch Fuse Holder**  
Catalog No. **CH143DNMSU-F**

## Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	50
Rated voltage			AC 690 V
Size			14 x 51 mm
Description			with microswitch replaces CH143BNMS-F
Number of poles			3P + N
usable for size/applications			C14G(A)S fuses
Standard/Approval			IEC
Standards/Regulations			IEC 60269-1

## Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Holder for cylindrical fuse (EC002705)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Holder for cylindrical fuse (ecl@ss10.0.1-27-14-21-21 [ADI305007])			
Nominal voltage		V	690
Mounting method			DIN rail
For fuse size			14x51 mm
Number of poles			3
Concurrently switching neutral conductor			No
Lockable			Yes
With optical defect indication			No
Width in number of modular spacings			6
Built-in depth		mm	51.5
Degree of protection (IP)			IP20