




Fuse enclosure +door, 6x3xE27, HxWxD=375x375x150mm

Part no. **RS27/I44E/T**
 Catalog No. **001885**

Delivery program


Product range			Ci insulated enclosures
Basic function			Enclosures with devices fitted
Product function			Individual fuse enclosures
Single unit/Complete unit			Stand-alone device
Degree of Protection			IP65
Description			Metric cable entry knockouts in all sides Transparent cover with quick-release fasteners PE/N bars Protective shroud with inscription label Fixing straps for wall fixing Sealable cover fasteners
Function			with 3 pole busbar mounting fuse bases on busbars, exchangeable from the front
Type cover			Transparent
Type Door			Transparent
Width		mm	375
Height		mm	375
Depth		mm	150
Rated operational current	I_e	A	25
Rated operational voltage	U_e	V AC	500
Max. fuse		A	25, DII/E27
Fused circuits		Number	18 x 1-pole 6 x 3-pole
PE and N terminals, quantity x cross-section		mm ²	On each: 2 x (6 - 35) On each: 18 x (1 - 6)

Notes
E



- 1 x M50/32
- 2 x M40/25
- 8 x M25/16
- 2 x M20

F



- 1 x M63/40
- 6 x M25/16
- 10 x M20
- 2 x M16

Notes ---PE/N bars
 Accessories for fuse enclosures →#090351
 Fuses, gauge pieces und screw caps
 →#288934
 →#288909
 →#100651

Technical data ETIM 6.0

Energy distribution systems (EG000015) / Switch fuse enclosure (EC002277)			
Electric engineering, automation, process control engineering / Electrical insulation and connecting material / Energy distribution system / Switch fuse enclosure (ecl@ss8.1-27-40-06-24 [ADI674004])			
Number of poles			3
Concurrently switching N-neutral			No
Nominal rated current		A	25
Nominal rated voltage		V	500
Number of groups			6
Protection			Screw fuse
Material housing			Plastic
Degree of protection (IP)			IP65
Height		mm	375
Width		mm	375
Depth		mm	150

Extension possible			Yes
Positioning on rail system			Universal
With transparent cover			Yes