

Miniature circuit breaker (MCB), 50A, 1p, C-Char, AC

Part no. PLHT-C50
247985
EL Number 1609504

General specifications			
Product name		Eaton Moeller series xPole - PLHT/-V MCB	
Part no.		PLHT-C50	
EAN		4015082479855	
Product Length/Depth		90 millimetre	
Product height		75 millimetre	
Product width		27 millimetre	
Product weight		0.222 kilogram	
Compliances		RoHS conform	
Product Tradename		xPole - PLHT/-V	
Product Type		MCB	
Product Sub Type		None	
Delivery program			
Application		Switchgear for industrial and advanced commercial applications	
Number of poles		Single-pole	
Number of poles (total)		1	
Number of poles (protected)		1	
Tripping characteristic		C	
Release characteristic		C	
Amperage Rating		50 A	
Type		Miniature circuit breaker PLHT	
Technical Data - Electrical			
Voltage type		AC	
Rated operational voltage (Ue) - max		230 V	
Rated insulation voltage (Ui)		440 V	
Rated impulse withstand voltage (Uimp)		4 kV	
Frequency rating - min		50 Hz	
Frequency rating - max		60 Hz	
Rated switching capacity (IEC/EN 60947-2)		25 kA	
Rated short-circuit breaking capacity (EN 60898) at 230 V		0 kA	
Rated short-circuit breaking capacity (EN 60898) at 400 V		0 kA	
Rated short-circuit breaking capacity (IEC 60947-2) at 230 V		25 kA	
Rated short-circuit breaking capacity (IEC 60947-2) at 400 V		25 kA	
Overvoltage category		III	
Pollution degree		2	
Technical Data - Mechanical			
Width in number of modular spacings		1.5	
Built-in depth		75 mm	
Degree of protection		IP20	
Connectable conductor cross section (solid-core) - min		2.5 mm ²	
Connectable conductor cross section (solid-core) - max		50 mm ²	
Connectable conductor cross section (multi-wired) - min		2.5 mm ²	
Connectable conductor cross section (multi-wired) - max		50 mm ²	
Design verification as per IEC/EN 61439 - technical data			
Rated operational current for specified heat dissipation (In)		50 A	
Heat dissipation per pole, current-dependent		0 W	
Equipment heat dissipation, current-dependent		5.1 W	

Static heat dissipation, non-current-dependent		0 W
Heat dissipation capacity		0 W
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		55 °C
Design verification as per IEC/EN 61439		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
Additional information		
Current limiting class		3
Features		Additional equipment possible
Special features		Ambient temperature hint: a 1 °C increase results in a 0.35% linear reduction of current carrying capacity
Used with		Miniature circuit breaker PLHT

Technical data ETIM 8.0

Circuit breakers and fuses (EG000020) / Automatsikring (EC000042)		
Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Miniature circuit breaker (MCB) (ecl@ss10.0.1-27-14-19-01 [AAB905014])		
Built-in depth	mm	75
Release characteristic		C
Number of poles (total)		1
Number of protected poles		1
Rated current	A	50
Rated voltage	V	230
Rated insulation voltage Ui	V	440
Rated impulse withstand voltage Uimp	kV	4
Rated short-circuit breaking capacity Icn according to EN 60898 at 230 V	kA	0
Voltage type		AC
Rated short-circuit breaking capacity Icn according to EN 60898 at 400 V	kA	0
Rated short-circuit breaking capacity Icu according to IEC 60947-2 at 230 V	kA	25
Rated short-circuit breaking capacity Icu according to IEC 60947-2 at 400 V	kA	25
Frequency	Hz	50 - 60
Current limiting class		3
Flush-mounted installation		No

Concurrently switching neutral conductor			No
Over voltage category			3
Pollution degree			2
Additional equipment possible			Yes
Width in number of modular spacings			1.5
Degree of protection (IP)			IP20
Ambient temperature during operating		°C	-25 - 55
Connectable conductor cross section multi-wired		mm ²	2.5 - 50
Connectable conductor cross section solid-core		mm ²	2.5 - 50
Explosion-proof			No