



Установочное реле с кнопкой, 24В, 1Н3

Тип **Z-R24/00**  
Каталог № **265189**

## Bauartnachweis nach IEC/EN 61439

| Технические характеристики для подтверждения типа конструкции |           |    |     |
|---|-----------|----|-----|
| Номинальный ток для указания потери мощности                  | $I_n$     | A  | 20  |
| Потеря мощности на полюс, в зависимости от тока               | $P_{vid}$ | W  | 2   |
| Потеря мощности оборудования, в зависимости от тока           | $P_{vid}$ | W  | 6.4 |
| Мин. рабочая температура                                      |           | °C | -20 |
| Макс. рабочая температура                                     |           | °C | 45  |

## Технические характеристики согласно ETIM 6.0

| Devices for distribution board-/surface mounting (EG000062) / Installation relay (EC001652)  |  |    |            |
|--|--|----|------------|
| Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Installation relay for distribution board (ec1@ss8.1-27-14-23-09 [AFZ821011]) |  |    |            |
| Function   |  |    | Mechanical |
| Mounting method  |  |    | DIN rail   |
| Width in number of modular spacings  |  |    | 1          |
| Built-in depth   |  | mm | 60         |
| Number of normally open contacts   |  |    | 0          |
| Number of normally closed contacts   |  |    | 2          |
| Number of change-over contacts   |  |    | 0          |
| Control voltage 1  |  | V  | 24 - 24    |
| Type of control voltage 1  |  |    | AC         |
| Frequency control voltage 1  |  | Hz | 50 - 50    |
| Control voltage 2  |  | V  | 0 - 0      |
| Type of control voltage 2  |  |    | -          |
| Frequency control voltage 2  |  | Hz | 0 - 0      |
| Nominal rated current  |  | A  | 20         |
| Supply voltage   |  | V  | 250 - 250  |
| Voltage type of supply voltage   |  |    | AC         |
| Max. incandescent lamp load  |  | W  | 0          |
| Max. load fluorescent lamp   |  | VA | 0          |
| Max. load fluorescent lamp (Duo circuit)   |  | VA | 0          |
| Max. load fluorescent lamp (parallel compensated)  |  | VA | 0          |
| Max. switching current (cos phi = 0.6)   |  | A  | 0          |

## Размеры

